




EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > CORCOM C SERIES MULTI-FUNCTION INLET FIL



Filter Type: **Power Entry Module**
Input Voltage Selection: **None**
Filter Switch Type: **DPST**
Filter Shield Type: **Filter Shield**
Product Orientation: **Vertical**

[All CORCOM C Series Multi-Function Inlet Fil \(8\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Entry Module
Filter Switch Type	DPST
Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Configuration Features

Extender Options	None
------------------	------

Electrical Characteristics

Input Voltage Selection	None
Leakage Current (Max) (120VAC, 60Hz)	250 μ A
Leakage Current (Max) (250VAC, 50Hz)	400 μ A



Current Rating	1 A
Operating Voltage	250 VAC

Body Features

Filter Shield Type	Filter Shield
Product Orientation	Vertical

Mechanical Attachment

Panel Mount Feature Type	Snap-In
--------------------------	---------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-102
CORCOM C SERIES MULTI-FUNCTION INLET FIL

TE Part # CAT-C8114-SR2
IEC Unfiltered Inlets, Corcom SR Series

TE Part # 1-1609112-4
15CBE1=F8274

TE Part # 4-1609134-7
20ESRM-3=F8277

Also in the Series | Corcom C

IEC Unfiltered Inlets(8)

Multi-Function Inlet Filters(8)

Customers Also Bought

TE Part #1-1879021-3
SMD Power Resistor: 7 Watt, 0.10-500 Ohm

TE Part #1-770174-0
04P MINI-UMNL ASSY V0 SNNI*

TE Part #2-1393222-0
V23061A1005A302=MINISTARKSTROM

TE Part #7-1393224-9
RY531012

TE Part #9-1393222-1
V23061B1005A301=MINISTARKSTROM

TE Part #1649329-4
RTE24012

TE Part #1393243-4
RTE24012

Documents

Product Drawings

1CFS1 S0=F7823

English

CAD Files

Customer View Model

ENG_CVM_CVM_6609113-2_D.3d_stp.zip



English

Customer View Model

[ENG_CVM_CVM_6609113-2_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6609113-2_D.3d_igs.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_6609113-2_0.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_6609113-2_0.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_6609113-2_0.2d_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE](#)

English

[1654001_Corcom_Product_Guide_C_Series](#)

English

[Corcom Combined Selector Charts](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English