

ATGBICS 8960-2602 IBM Compatible Transceiver SFP+ 16G Short Wave Fibre Channel DOM

Brand : ATGBICS

Product code: 8960-2602-C

Product name : 8960-2602 IBM Compatible Transceiver SFP+ 16G Short Wave Fibre Channel DOM



8960-2602 IBM Compatible Transceiver SFP+ 16G Short Wave Fibre Channel DOM


ATGBICS 8960-2602 IBM Compatible Transceiver SFP+ 16G Short Wave Fibre Channel DOM:

ATGBICS 8960-2602 16GBase Short Wave Fibre Channel SFP+ with an LC connector. Digital optical monitoring (DOM) support is also present enabling real-time monitoring of the parameters of the fibre optic transceiver. Our product meets the specification of IBM 8960-2602= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.



ATGBICS 8960-2602 IBM Compatible Transceiver SFP+ 16G Short Wave Fibre Channel DOM. SFP transceiver type: Fiber optic, Maximum data transfer rate: 16000 Mbit/s, Interface type: SFP+. Product colour: Silver, Housing material: Metal, Country of origin: United Kingdom. Input voltage: 3.3 V, Maximum voltage: 3.5 V, Power consumption (typical): 1 W. Width: 13.4 mm, Depth: 56.5 mm, Height: 8.5 mm. Number of products included: 1 pc(s), Package type: Box

Performance		Operational conditions	
SFP transceiver type *	Fiber optic	Maximum operating temperature	70 °C
Maximum data transfer rate *	16000 Mbit/s	Operating temperature (T-T)	0 - 70 °C
Interface type *	SFP+	Storage temperature (T-T)	-40 - 85 °C
Fiber optic connector	LC	Operating relative humidity (H-H)	0 - 95%
Ethernet LAN	✓	Storage relative humidity (H-H)	0 - 95%
Ethernet interface type	16 Gigabit Ethernet	Weight & dimensions	
Digital Diagnostics Monitoring (DDM)	✓	Width	13.4 mm
Features		Depth	56.5 mm
Product colour	Silver	Height	8.5 mm
Housing material	Metal	Weight	19 g
Plug and Play	✓	Packaging data	
Hot-swap	✓	Number of products included	1 pc(s)
Easy to install	✓	Package type	Box
Country of origin	United Kingdom	Technical details	
Brand compatibility	IBM	Sustainability compliance	✓
Certification	CE, FCC, RoHS	Sustainability certificates	RoHS
Power		Doesn't contain	Lead
Input voltage	3.3 V		
Maximum voltage	3.5 V		
Power consumption (typical)	1 W		



5056468747020

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.