

2-1969614-4 ✓ ACTIVE

VAL-U-LOK


TE Internal #: 2-1969614-4

Rectangular Power Connectors, Housing, Receptacle, Wire-to-Wire,
24 Position, 4.2 mm [.165 in] Centerline, Wire & Cable, UL 94V-0

[View on TE.com >](#)



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Wire**

Number of Positions: **24**

Centerline (Pitch): **4.2 mm [.165 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	24
Number of Rows	2

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Retention Within Housing	Without
Contact Type	Receptacle

Termination Features

Termination Method to Wire & Cable

Crimp

Mechanical Attachment

Connector Mounting Type

Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)

4.2 mm [.165 in]

Housing Color

Natural

Housing Material

Nylon 6/6

Dimensions

Connector Height

11.7 mm [.461 in]

Product Width

19.8 mm [.779 in]

Product Length

51.6 mm [2.031 in]

Row-to-Row Spacing

4.2 mm [.165 in]

Usage Conditions

Operating Temperature Range

-40 – 105 °C [-40 – 221 °F]

Operation/Application

Circuit Application

Power & Signal

Industry Standards

CSA Rating

208567

UL Rating

Recognized

Agency/Standard

CSA, UL

Approved Standards

UL E28476

UL Flammability Rating

UL 94V-0

Glow Wire Rating

Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity

500

Packaging Method

Bag

Product ComplianceFor compliance documentation, visit the product page on TE.com

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023

(235)

Candidate List Declared Against: JAN 2021

(211)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2-1586018-4
24P PM PLUG VAL-U-LOK V0TE Part # 2-1586017-4
24P FH PLUG VAL-U-LOK V0TE Part # 2-1969613-4
24P PM PLUG VAL-U-LOK V0TE Part # 2-1969612-4
24P FH PLUG VAL-U-LOK V0

Customers Also Bought

TE Part #6706090001
TMS-SCE-1-1/2-2.0-4TE Part #745253-2
20 DF SCKT CONT,PLTDTE Part #745254-2
20DF PIN CONTACT,PLATEDTE Part #60617-4
CMNL SOK PTPPHBZ L/P



Documents

Product Drawings

24P RCPT VAL-U-LOK V0

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-1969614-4_A_c-2-1969614-4-a.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1969614-4_A_c-2-1969614-4-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1969614-4_A_c-2-1969614-4-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773730-3 VAL-U-LOK Connectors with TPA Flyer

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English