

213337-1

✓ ACTIVE

AMP

TE Internal #: 213337-1

Rectangular Caps & Covers, Dust Cover, -65 – 125 °C [-85 – 257 °F]

[View on TE.com >](#)

Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Caps & Covers

Connector Cover Type: **Dust Cover**

Sealable: **No**

Operating Temperature Range: **-65 – 125 °C [-85 – 257 °F]**

Features

Product Type Features

Connector Cover Type	Dust Cover
Sealable	No

Usage Conditions

Operating Temperature Range	-65 – 125 °C [-85 – 257 °F]
-----------------------------	-----------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #640923-1
RECEPT,PIDG FASTON 22-18 110



TE Part #1757820-8
AMPLIMITE,ASY,RCPT,STD,109,ZN,3,CT



TE Part #234062-002
2524E0114-9



TE Part #675714-000
SO96-3-00



TE Part #201595-000
SO96-2-00



TE Part #532430-3
HDI PIN ASSY 2 ROW 40 POS



TE Part #3-2176554-9
3430 A2 1% 36R 100ppm 1k RL



TE Part #4-2176554-0
3430 A2 1% 39R 100ppm 1k RL



TE Part #8-2176483-1
RA73F 2A 3K74 0.1% 5K RL



TE Part #1617032-2
HFW1201S103 = HFW 1/2 SIZE REL

Documents

Product Drawings

[DUST COVER,MIL 600](#)

English

Datasheets & Catalog Pages

[ARINC 600 Next Generation Receptacle Connector](#)

English