



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH DT Receptacle Connectors



Connector System: **Wire-to-Wire**
Number of Positions: **2**
Connector & Housing Type: **Housing for Male Terminals**
Centerline (Pitch): **5.46 mm [.215 in]**
Sealable: **Yes**

[All DEUTSCH DT Receptacle Connectors \(241\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Blank Cavity Position	0
Number of Positions	2
Number of Rows	1

Electrical Characteristics

--	--



Operating Voltage	250 VAC
Nominal Voltage Architecture	12 V, 24 V, 48 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	Size 16
Contact Type	Pin
Mating Pin Diameter	1.59 mm[.063 in]
Contact Current Rating (Max)	13 A

Mechanical Attachment

Terminal Position Assurance	Yes
Strain Relief	Add By Accessory
Mating Alignment Type	Polarized
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA GF
Centerline (Pitch)	5.46 mm[.215 in]

Dimensions

Connector Height	17.02 mm[.67 in]
Product Width	17.15 mm[.675 in]
Product Length	46.18 mm[1.818 in]
Compatible Insulation Diameter Range	2.23 – 3.68 mm[.088 – .145 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Degree of Protection	IP68, IP6K9K
Agency/Standard	SAE J2030



UL Flammability Rating	12mm Flame Test per Standard UL-94
------------------------	------------------------------------

Packaging Features

Packaging Quantity	950
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>
















EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 <p>TE Part # CAT-D487-W416 WedgeLocks: DEUTSCH DT</p>	 <p>TE Part # CAT-D48-SP729 DEUTSCH Sealing Plugs</p>	 <p>TE Part # CAT-D48-ST273 DEUTSCH Solid Contacts</p>	 <p>TE Part # CAT-D487-M8649 DEUTSCH DT Mounting Clips</p>
 <p>TE Part # CAT-J41-DDPC DEUTSCH DT Plug Connectors</p>	 <p>TE Part # CAT-J67-DSCC16 DEUTSCH Size 16 Crimp Contacts</p>	 <p>TE Part # 1924487-2 MOUNTING CLIP, AMPSEAL 16</p>	 <p>TE Part # DT-RT1 EXT TOOL, FRONT RELEASE</p>
 <p>TE Part # 2300908-1 0460-003-16329, PIN, SOLID, 20-24AWG, AU</p>	 <p>TE Part # 1-2303815-1 DT06-2S-TE31, PLG, 2P, GRY, E, SNAPCAP</p>	 <p>TE Part # 1-2303815-4 DT06-2S-TE32, PLG, 2P, BLK, E, SNAPCAP</p>	 <p>TE Part # 2-2303815-1 DT06-2S-TE81, PLG, 2P, GRY, E, SNAPXCAP</p>
 <p>TE Part # 1-2303815-3 DT06-2S-TN32, PLG, 2P, BLK, N, SNAPCAP</p>	 <p>TE Part # DT06-2S-CE02 PLG, 2P, BLK, E</p>	 <p>TE Part # CAT-D48-SFT273 DEUTSCH Stamped and Formed Contacts</p>	

Also in the Series | DEUTSCH DT

 <p>Automotive Connector Caps & Covers (47)</p>	 <p>Automotive Connector Locks & Position Assurance(74)</p>	 <p>Automotive Housings(620)</p>	 <p>Connector Backshells(58)</p>
--	--	---	---



Connector Seals & Cavity Plugs(6)

Insertion & Extraction Tools(3)

Other Automotive Connector Accessories(27)

PCB Headers & Receptacles(103)

Customers Also Bought

TE Part #776428-3
AS 16, 2P CAP ASSY, KEY 3

TE Part #3-5177986-4
0.8FH,P08H.5,100,08/Sn,TR,SC

TE Part #2071366-1
EW60-1A3-BL12D04,00000

TE Part #5223979-1
UPM GUIDE MODULE

TE Part #1473562-3
RITS CONN. PLUG ASSY 3P YELLOW

TE Part #1-2303812-1
DT04-2P-TE31, REC, 2P, GRY, E, SNAPCAP

TE Part #6862-201-16278
CONT SOC

Documents

Product Drawings
DT04-2P-TN32, REC, 2P, BLK, N, SNAPCAP
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-2303812-3_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1-2303812-3_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1-2303812-3_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Product Specifications

Application Specification

English

Agency Approvals

UL Report

English