




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance > DEUTSCH DRB Wedgelocks



Connector & Contact Retention Accessory Type: **Secondary Lock**

Primary Product Color: **Gray**

Primary Product Material: **PBT**

Number of Positions: **102**

Sealable: **No**

[All DEUTSCH DRB Wedgelocks \(20\)](#)

Features

Product Type Features

Connector & Contact Retention Accessory Type	Secondary Lock
Sealable	No

Configuration Features

Number of Positions	102
---------------------	-----

Body Features

Primary Product Color	Gray
Primary Product Material	PBT

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------



Packaging Features

Packaging Quantity	216
Packaging Method	Box

Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D781-CH8172
DEUTSCH DRB Housings

Also in the Series | DEUTSCH DRB

Automotive Connector Caps & Covers
(2)

Automotive Connector Locks &
Position Assurance(20)

Automotive Housings(19)

Insertion & Extraction Tools(1)

Other Automotive Connector
Accessories(6)

Customers Also Bought

TE Part #DRB16-128SAE-L018
DEUTSCH DRB Housings

TE Part #WB-51PAR
DEUTSCH DRB Wedgelocks

TE Part #4-1670901-1
12POS,AMP MCP2.8,REC HSG,ASSY

TE Part #DT06-08SA-CE05
PLG, 8P, GRY, E, SEAL RET, CAP, A

TE Part #DRB102-BT
BOOT, 102P, PLG/REC, ST, BLK

TE Part #K1132223
Toggle Switch 07-2-2-15 A 905

TE Part #YDRBM-3A0000000000
FLANGE, MOUNT, 102/128P, BLK,
STUD, A



Documents

Product Drawings

WEDGE LOCK, 102P, REC, GRY, LF, DRB, A

English

CAD Files

Customer View Model

ENG_CVM_CVM_WB-51PAL_99.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_WB-51PAL_99.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_WB-51PAL_99.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English