



Economy Power 2.5

TE Internal #: 1-1969590-5
Housing, Receptacle, Wire-to-Panel / Wire-to-Wire, 15 Position, .098 in [2.5 mm] Centerline, Crimp, 1 Row, White, Mating Retention, Economy Power 2.5

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Panel, Wire-to-Wire**
Number of Positions: **15**
Centerline (Pitch): **2.5 mm [.098 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	15
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features

Primary Product Color	White
-----------------------	-------

Contact Features

--	--



Contact Type	Pin
Contact Base Material	Brass
Contact Current Rating (Max)	7.5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	With
PCB Mount Retention	Without
Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Entry Configuration	Both Ends Closed
Housing Material	Nylon - GF
Centerline (Pitch)	2.5 mm[.098 in]

Dimensions

Connector Length	40 mm[1.575 in]
Connector Height	6.6 mm[.26 in]
Connector Width	18.17 mm[.715 in]
Compatible Insulation Diameter Range	1.3 – 1.7 mm[.051 – .067 in]
Wire Size	.13 – .33 mm ²

Usage Conditions

Operating Temperature Range	-25 – 105 °C[-13 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	800
Packaging Method	Bag



Other

Discrete Wire Connector Comment	Panel Mount
---------------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




 TE Part # 1969590-4 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5	 TE Part # 1969590-3 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5	 TE Part # 1969590-2 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5	 TE Part # 1-1969590-0 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5
--	---	--	--



 TE Part # 1969590-5 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5	 TE Part # 1969590-6 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5	 TE Part # 1969590-7 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5	 TE Part # 1969590-8 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5
 TE Part # 1969590-9 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5	 TE Part # 1-1969590-1 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5	 TE Part # 1-1969590-2 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5	 TE Part # 1-1969590-3 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5
 TE Part # 1-1969590-4 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5	 TE Part # 1-1969591-5 HSG,REC,PANEL MOUNT,GWT, SINGLE ROW,EP2.5	 TE Part # 2314712-2 HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5	

Also in the Series


Economy Power 2.5

 PCB Headers & Receptacles(494)	 PCB Latches, Locks & Retainers(49)	 Rectangular Power Connectors(43)	 Wire-to-Board Connector Assemblies & Housings(311)
 Wire-to-Board Connector Contacts(6)			


Customers Also Bought




TE Part #440452-000
RT-3-NO.1-0.2.25IN



TE Part #521081-1
ULTRA-POD 250 ASSY REC 18-14
AWG BR




TE Part #1-521253-3
PL MKIII & FASTON 250 HSG 2P
NYLON GREEN



TE Part #1-853088-0
ANVIL




TE Part #1855118-1
U POD .187 STRAIGHT SAPR090F140F
LM & G




TE Part #2-1241817-3
STD TIM HOUSING MKII 3POS



TE Part #938365P002
VERSAFIT-1/8-0-0.75IN-ST



TE Part #644267-2
SL156 HSG (YELLOW)



TE Part #1217972-2
250 FASTON, FLAG, REC., 18-14 AWG,
NPST

Documents

Product Drawings

HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1969590-5_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1969590-5_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1969590-5_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English