Compact N-Type Cal. Kits

3-in-1 DC to 6,8 GHz



Withwave's Compact N-Type Calibration Kits offers excellent performance characteristics that is specially designed for the fine-tuning in production environments and quality testing facilities using 50 ohm N-type connectors from DC to 6, 8 GHz.

This Cal. Kit include all needed calibration standard (Open, Short, Load) in one unit. It is best solution for available for ease of use in VNA calibration, especially in the field.



Features

- DC to 6, 8 GHz
- Standard kit included N-type (Male) OPEN-SHORT-LOAD

Application

- VNA, Full 2-port CAL.
- Test & Measurement
- Precision Calibration

Specification

Scope	Items	WWNT(M)	WWNT(M)-8G
Electrical	Freq. range	DC to 6 GHz	DC to 8 GHz
	Impedance	50 Ohm	
	Return loss (LOAD)	< -38 dB (DC to 6 GHz)	< -42 dB (DC to 6 GHz) <-37 dB (6 to 8 GHz)
	Phase deviation (OPEN,SHORT)	< 1.5	degrees
Mechanical	Connector type	N-Type (Male)	
	Housing	Stainless steel	
	Weight	177 g	


3-in-1 DC to 6 GHz



■ Calibration Coefficient

Type	Cal. Coefficient		
OPEN	C0	89.939x10 ⁻¹⁵ F	
	C1	2536.80x10 ⁻²⁷ F/Hz	
	C2	$-264.990 \times 10^{-36} \text{F/Hz}^2$	
	C3	$13.4x10^{-45}F/Hz^3$	
	Offset delay	40.856 ps	
	Offset Loss	$0.93~\mathrm{G}\Omega/\mathrm{s}$	
	L0	3.3998x10 ⁻¹² H	
	L1	-496.4808x10 ⁻²⁴ H/Hz	
SHORT	L2	$34.8314x10^{-33}H/Hz^{2}$	
5115111	L3	$-0.7847x10^{-42}H/Hz^3$	
	Offset delay	45.955 ps	
	Offset Loss	$1.087~\mathrm{G}\Omega/\mathrm{s}$	

Drawing



Unit: mm