



Timer Connector System

TE Internal #: 1-1718093-1

PCB Mount Header, Vertical, Wire-to-Board, 42 Position, 4 mm [.157 in] Centerline, Fully Shrouded, Tin, Through Hole - Solder, Timer Connector System

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles > Low & Medium Power Header



Connector System: **Wire-to-Board**

Number of Positions: **42**

Centerline (Pitch): **4 mm [ .157 in ]**

Sealable: **No**

PCB Mount Orientation: **Vertical**

[All Low & Medium Power Header \(168\)](#)

Features

Product Type Features

Mixed & Hybrid Header	Yes
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Header Type	Fully Shrouded
Connector System	Wire-to-Board
Sealable	No

Configuration Features

Number of Sections	1
Number of Signal Positions	42
Number of Positions	42
PCB Mount Orientation	Vertical
Number of Rows	3



Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Size	1.6mm, 2.8mm
Contact Type	Tab
Mating Tab Width	1.6 mm, 2.8 mm [.062 in][.11 in]
Mating Tab Thickness	.6 mm, .8 mm [.023 in][.031 in]
Contact Mating Area Plating Material	Tin

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

Mounting Holes	Without
Mating Alignment	With
PCB Mount Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	Without

Housing Features

Centerline (Pitch)	4 mm [.157 in]
--------------------	----------------

Dimensions

Connector Length	73.2 mm [2.88 in]
Connector Width	37.1 mm [1.46 in]
Profile Height from PCB	32.5 mm [1.27 in]

Operation/Application

Shielded	No
Circuit Application	Signal

Packaging Features

Packaging Type	Box
Packaging Quantity	16

Other

Interface Number	1-967281-1
------------------	------------

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-967281-1  
MICRO-T2/JPT GEH42P



TE Part # 963225-1  
DICHUNG F 42P GEH

Also in the Series | Timer Connector System



Automotive Connector Caps & Covers (12)



Automotive Connector Locks & Position Assurance(17)



Automotive Housings(234)



Automotive Terminals(145)



Connector Seals & Cavity Plugs(32)



Crimp Terminal Housings(13)




Insertion & Extraction Tools(18)



Other Automotive Connector Accessories(1)




PCB Headers & Receptacles(82)



Quick Disconnects(4)

Customers Also Bought



TE Part #1-967280-1  
MESSERLEISTE MIX42P



TE Part #1-1564530-1  
Heavy Duty Sealed Connector Series Housings



TE Part #929941-1  
JPT REC 2.8 Contact SWS Sn



TE Part #1564324-1  
AMP MCP 1.5K, CONTACT, SWS



TE Part #2600030-2  
4CCT GREY RECEP W/SMALL SEAL



TE Part #BSA107N00420136000  
923 PLUG, SHORT, SPEEDTEC



TE Part #BSA108N00480136000  
923 PLUG, SHORT, SPEEDTEC

Documents



Product Drawings

MIXED TAB HEADER,42POS

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_1-1718093-1\_A.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-1718093-1\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-1718093-1\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

42 POS. Coupling For JUNIOR-POWER-TIMER / MICRO-TIMER and STITCH-TAB

English

Product Specification

English