

175133-8 ✓ ACTIVE

TE Internal #: 175133-8


PCB Connector Mounting, 8 Position, .079 in [2 mm] Centerline, 28

– 24 AWG Wire Size, Natural, -22 – 221 °F [-30 – 105 °C]

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Hardware > PCB Connector Mounting



Number of Positions: 8

Centerline (Pitch): 2 mm [.079 in]

Wire Size: 28 – 24 AWG

Primary Product Color: Natural

Operating Temperature Range: -30 – 105 °C [-22 – 221 °F]

Features

Configuration Features

Number of Positions	8
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Housing Features

Centerline (Pitch)	2 mm [.079 in]
--------------------	----------------

Dimensions

Product Width	7.55 mm [.297 in]
---------------	-------------------

Product Length	12.29 mm [.484 in]
----------------	--------------------

Product Height	6.65 mm [.261 in]
----------------	-------------------

Wire Size	28 – 24 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
-----------------------------	-----------------------------

Packaging Features

Packaging Quantity	1000
--------------------	------

Packaging Method

Bag

Other

Connector Accessory Comment

For Use With CT Connector, Two receptacle connectors are applied per holder.

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)

Candidate List Declared Against: JUNE 2023 (235)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 173977-8
CT CONN MT REC ASSY 8P

Customers Also Bought



TE Part #1-179554-3
DYNAMIC D-3200 WTW TAB HSG 6P



TE Part #174259-2
ECONOSEAL, CONNECTOR
HOUSING



TE Part #173977-4
CT CONN MT REC ASSY 4P



TE Part #171822-2
EIS REC. HSG 2P-NATURAL



TE Part #171661-1
E-J MK-2 070 TAB CONT



TE Part #1420011-3
GET CONNECTOR



TE Part #1-102541-0
24 AMPMODU MT COVER DR .100CL



TE Part #1-640383-9
19P MTA156 HDR ASSY STR SQ SN

Documents

Product Drawings

[CT DBL ROW 8P HOLDER 8P NATURA](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_175133-8_E.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_175133-8_E.3d_igs.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_175133-8_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[CSA Certificate](#)

English

