

184452-1

✓ ACTIVE

## Sealed Sensor Connector SSC System

TE Internal #: 184452-1

Housing for Female Terminals, Wire-to-Device / Wire-to-Wire / Wire-to-Board, 6 Position, .197 in [5 mm] Centerline, Sealed Sensor Connector SSC System

[View on TE.com >](#)

Connectors &gt; Automotive Connectors &gt; Automotive Housings

Connector System: **Wire-to-Board, Wire-to-Device, Wire-to-Wire**Number of Positions: **6**Connector & Housing Type: **Housing for Female Terminals**Centerline (Pitch): **5 mm [.197 in]**Sealable: **Yes****Features****Product Type Features**

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Board, Wire-to-Device, Wire-to-Wire
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Primary Locking Feature	Integrated in Housing

**Configuration Features**

Blank Cavity Position	3, 6
Number of Positions	6
Number of Rows	1

**Electrical Characteristics**

Operating Voltage	125 VAC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V, 80 V, 90 V, 125 V

**Body Features**

Cable Exit Angle	180°
Primary Product Color	Black
Connector & Keying Code	A

### Contact Features

Contact Size	1.8mm
--------------	-------

### Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	Without
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

### Housing Features

Housing Material	PBT GF
Centerline (Pitch)	5 mm [.197 in]

### Dimensions

Connector Height	27.6 mm [1.09 in]
Product Width	24.8 mm [.976 in]
Product Length	43.2 mm [1.7 in]

### Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C [158 °F] [167 °F] [176 °F] [185 °F] [194 °F] [212 °F] [221 °F] [230 °F] [248 °F] [257 °F]
Operating Temperature Range	-40 – 125 °C [-40 – 257 °F]

### Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

### Packaging Features

Packaging Quantity	800
Packaging Method	Package

### Other

Serviceable	Yes
Connector Position Assurance Capable	No

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>


EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------


EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

## Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts


			
TE Part # 184141-1 WIRE SEAL, RUBBER, SENSOR, PURPLE, LIM	TE Part # 184140-1 WIRE SEAL, RUBBER, SENSOR, ORANGE	TE Part # 184060-1 6 POS./6 CIRC PLUG ASSY, KEY A	TE Part # 184030-3 RECPT, CONTACT 070, PTPPHBZ
			
TE Part # 184030-1 RECPT, CONTACT 070, AUPHBZ	TE Part # 184095-1 RECPT, CONTACT .070, AUPHBZ	TE Part # 184095-2 RECPT, CONTACT .070, PTPPHBZ	TE Part # 184139-1 WIRE SEAL, RUBBER, SENSOR, BLUE



## Also in the Series | Sealed Sensor Connector SSC System



## Customers Also Bought



## Documents

### Product Drawings

#### 6 POS SSC PLUG ASSY, BLKD CKTS

English

---

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_184452-1\\_A.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_184452-1\\_A.3d\\_stp.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_184452-1\\_A.2d\\_dxf.zip](#)

English

### 3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

#### Sealed Sensor Connector (SSC) System

English

---

### Product Specifications

#### Application Specification

English