




Connectors > Circular Connectors > Standard Circular Connectors



Sealable: **No**

Contact Current Rating (Max): **14 A**

Circuit Application: **Power**

Shell Base Material: **Brass**

Circular Connector Shell Size: **15**

Features

Product Type Features

Sealable	No
Shell Type	Metal

Body Features

Shell Base Material	Brass
---------------------	-------

Contact Features

Contact Current Rating (Max)	14 A
Circular Connector Contact Type	Pin

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Housing Features

Circular Connector Shell Size	15
Alignment Keyed	0°

Operation/Application

Durability Rating	500 Cycles
-------------------	------------



Circuit Application

Power

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (1.5% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer









This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # EEA201M01000500000 915 ITEC RECEPTACLE	 TE Part # C0-0201-000-000 CRIMPING TOOL MID-SIZE	 TE Part # C0-0235-000-000 DIGITAL CRIMPING TOOL, SMALL	 TE Part # C0-0258-000-000 POSITIONING INSERT FOR 1 MM CONTACTS
---	--	---	---

Customers Also Bought



 TE Part #BGC106M14001116000 923 RECEPTACLE, ANGLED, ROTATABLE	 TE Part #BGC110N00001216000 923 RECEPTACLE, ANGLED, ROTATABLE	 TE Part #22-0447-031-000 923 RECEPTACLE, ANGLED, IG3B, ROTATABLE	 TE Part #353199-4 F07A PCF PLUG CA ASSY L=5000
 TE Part #8A-0056-000-000 615-915 HAT STOPPER VA WITH L- SEALING	 TE Part #AGC138M83001115000 623 receptacle angled rotatable	 TE Part #BEA127M10000105000 923 receptacle, speedtec	 TE Part #C6-0178-000-000 lid tool
 TE Part #EKA205F03330003000 915 EXTENSION	 TE Part #ESA204M03320003000 915 PLUG		

Documents

Product Drawings
CONTACT PIN 1 MM

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_61-0231-011-000_B.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_61-0231-011-000_B.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_61-0231-011-000_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[Pin 1mm 61.231.11](#)

English

[Product Environmental Compliance](#)

[TE Material Declaration](#)

English