

1218434-3

✓ ACTIVE

AMPLIMITE

TE Internal #: 1218434-3


Box Mount D-Sub Connectors, Receptacle, Round Termination

Post & Tail Diameter .76 mm [.03 in], Cable-to-Board, 25 Position, 3

Connector Shell Size

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors

Connector & Housing Type: **Receptacle**Round Termination Post & Tail Diameter: **.76 mm [.03 in]**Connector System: **Cable-to-Board**Number of Positions: **25**Power/Signal/Coax Combination: **No****Features****Product Type Features**

| | |
|-----------------------------------|-----------------------|
| Connector & Housing Type | Receptacle |
| Connector System | Cable-to-Board |
| Connector Shell Size | 3 |
| Sealable | No |
| Connector & Contact Terminates To | Printed Circuit Board |

Configuration Features

| | |
|-------------------------------|-------------|
| PCB Mount Orientation | Right Angle |
| Number of Positions | 25 |
| Power/Signal/Coax Combination | No |

Body Features

| | |
|------------------------------------|-----------|
| Rear Shell Material | Steel |
| Rear Shell Plating Material | Cadmium |
| Front Shell Plating Material | Cadmium |
| Front Shell Material | Steel |
| D-Sub Connector Insert Arrangement | MS18275-1 |

Contact Features

| | |
|--------------------------------------|-------------|
| | 50 μ in |
| Contact Mating Area Plating Material | Gold |

| | |
|---|-------------------------|
| PCB Contact Termination Area Plating Material | Nickel |
| Contact Base Material | Beryllium Copper, Brass |
| Contact Type | Socket |
| Contact Size | Size 20 |
| Contact Current Rating (Max) | 5 A |

Termination Features

| | |
|--|-------------------|
| Termination Post & Tail Length | 3.18 mm [.125 in] |
| Round Termination Post & Tail Diameter | .76 mm [.03 in] |

Mechanical Attachment

| | |
|------------------------|---------|
| Mounting Hole Diameter | 2.92 mm |
| Mating Alignment | Without |

Housing Features

| | |
|--------------------|-------------------|
| Centerline (Pitch) | 2.77 mm [.109 in] |
|--------------------|-------------------|

Usage Conditions

| | |
|-----------------------------|-----------------------------|
| Operating Temperature Range | -55 – 125 °C [-67 – 257 °F] |
|-----------------------------|-----------------------------|

Operation/Application

| | |
|---------------------|--------|
| Circuit Application | Signal |
|---------------------|--------|

Packaging Features

| | |
|------------------|---------|
| Packaging Method | Package |
|------------------|---------|

Other

| | |
|-----------------------------|--|
| D-Shaped Connectors Comment | For solder dip product see part number 1218434-8. |
|-----------------------------|--|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Not Compliant |
| EU ELV Directive 2000/53/EC | Not Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Cd (8.18% in shell) |

Pb (3.7% in socket)

Article Safe Usage Statements:

Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #5188834-1
Z-PACK/A M-HDR 154P.




TE Part #5-1879208-0
CPF 0402 1K1 0.1% 25PPM 1K RL



TE Part #3-1879216-4
CPF0402 180K 0.1% 25PPM 1K RL



TE Part #YDTS26F17-35SAV001
PLUG ASSY



TE Part #532433-8
HDI PIN ASSY 3 ROW 165 POS



TE Part #251379-000
SO63-3-55-24-90



TE Part #021174-000
SO63-2-55-22-90



TE Part #443976-4
AMPLIMITE, ASY, RCPT, POSTD, 109,4



TE Part #6-534998-0
20 MODIV VRT DR CE 100/125

Documents

Product Drawings

[R/A RCP ASSY 25 POS SER 109](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_1218434-3_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_1218434-3_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1218434-3_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[UL Report](#)

English