

RF TERMINATION

Type 6506.17.B

Description

Standard Termination, Medium Power



Product Configuration

Connector	N jack (female)
Interface standards	IEC 60169-16_MIL-STD-348A/304_CECC 22210

Technical Data

Electrical Data

Nominal Impedance	50 Ω			
Frequency range	0 to 12.4 GHz			
Frequency sub range	DC to 1 GHz	1 to 4 GHz	4 to 10 GHz	10 to 12.4 GHz
VSWR max.	1.05	1.1	1.2	1.25
Power rating	6 Watt average power up to 40 °C ambient temperature, linearly derated to 0 Watt at 130 °C ambient temperature. 1000 Watt peak power , 5 μ s pulse, 0.05 % duty cycle			

Mechanical Data

Weight	0.057 kg
--------	----------

Environmental Data

Operating temperature	-40 °C to 130 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Part	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Stainless Steel	
Body	Aluminium	Anodized
Insulator	Air Dielectric - Bead - PS	

Related Documents

Outline drawing	DOU-00005441
-----------------	--------------

Ordering Information

Single Packaging Packaging	6506.17.B
-------------------------------	-----------

Additional Information

Important note	WARNING Beryllia Ceramic Inside! DO NOT sand, scrap or tamper with. Dispose in accordance with all relevant regulations.
----------------	--