

**1651003-2**

✓ ACTIVE

**RAPID LOCK**

TE Internal #: 1651003-2

Insulation Boots &amp; Sleeves, Insulation Boot, PVC, Red, Bag, -40 – 221 °F [-40 – 105 °C]

[View on TE.com >](#)

Terminals &amp; Splices &gt; Terminal Housings, Insulation Sleeves &amp; Blocks &gt; Insulation Boots &amp; Sleeves

Insulation Boot & Sleeve Product Type: **Insulation Boot**Primary Product Material: **PVC**Primary Product Color: **Red**Packaging Method: **Bag**Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]****Features****Product Type Features**

Insulation Boot &amp; Sleeve Product Type

Insulation Boot

**Body Features**

Primary Product Material

PVC

Primary Product Color

Red

**Dimensions**

Product Length

47.7 mm[1.878 in]

**Usage Conditions**

Operating Temperature Range

-40 – 105 °C [-40 – 221 °F]

**Industry Standards**

UL Flammability Rating

UL 94V-0

**Packaging Features**

Packaging Quantity

100

Packaging Method

Bag

## Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 TE Part # 6648235-1 CROWN,SKT,#4	 TE Part # 1410354-7 MULTI-GIG GUIDEPIN, 9MM 2.60
--	---

## Customers Also Bought



## Documents

### Product Drawings

[901-0121-32034=BOOT,INSULATING](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_1651003-2\\_C.2d\\_dxf.zip](#)

English

### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1651003-2\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1651003-2\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[POWER\\_CONNECTORS\\_CATALOG\\_SEC02\\_CABLE\\_MOUNTED](#)

English

### Busbar Power Brochure

English

### Product Specifications

[Application Specification](#)

English

**Agency Approvals**

**Agency Approval Document**

English