172051-3 ✓ ACTIVE

MTEI

TE Internal #: 172051-3

Connector Assembly, Receptacle, Wire-to-Board, 3 Position, .098 in

[2.5 mm] Centerline, Insulation Displacement (IDC), 1 Row, Red,

MTEI

View on TE.com >



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings











Connector Product Type: Connector Assembly

Connector & Housing Type: Receptacle

Connector System: Wire-to-Board

Number of Positions: 3

Centerline (Pitch): 2.5 mm [.098 in]

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Configuration Features	
Number of Positions	3
Number of Rows	1
Electrical Characteristics	
Operating Voltage	250 VAC
Body Features	
Primary Product Color	Red
Contact Features	



Contact Retention Within Housing	With
Contact Type	Socket
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	3.5 A
Termination Features	
Termination Method to Wire & Cable	Insulation Displacement (IDC)
Mechanical Attachment	
Strain Relief	Without
Contact Retention Type Within Housing	Locking Lance
Panel Mount Feature	Without
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Housing Material	Nylon 66
Centerline (Pitch)	2.5 mm[.098 in]
Dimensions	
Connector Length	10 mm[.394 in]
Connector Height	13.8 mm[.543 in]
Compatible Insulation Diameter Range	1.1 – 1.5 mm[.043 – .059 in]
Wire Size	$.34 \text{ mm}^2$
Usage Conditions	
Operating Temperature Range	-20 - 95 °C[-4 - 203 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	
Agency/Standard	UL
Approved Standards	UL Recognized
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Quantity	700
Packaging Method	Bag



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Melamine (3% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Also in the Series | MTEI



Customers Also Bought







Documents

Product Drawings

3P MTEI RCPT HSG ASY 22

English

3P MTEI RCPT HSG ASY 22

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_172051-3_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_172051-3_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_172051-3_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

1-1773972-5_EIS_Connectors_Brochure

English

Product Specifications

Terminating AMP MTEI Connector

English

Application Specification

English

Product Environmental Compliance

Product Compliance Document

English

Product Compliance Document

English



Instruction Sheets

Instruction Sheet (non U.S.)

Japanese

Instruction Sheet (non U.S.)

Japanese

PISTOL TOOL, MTEI

Japanese

Instruction Sheet (non U.S.)

Japanese

Agency Approvals

Agency Approval Document

English