



EMI & EMC Solutions > EMI Shielding > EMI Gaskets > Extruded EMI Gasket Conductive Strip



Gasket Type: Extruded EMI Gasket

Finished Type: Conductive Strip

Binding Material: Silicone

Filler Material: Nickel Plated Graphite (Ni/C)

Gasket Shape: Tube

[All Extruded EMI Gasket Conductive Strip \(56\)](#)

Features

Product Type Features

Finished Type	Conductive Strip
Binding Material	Silicone
Filler Material	Nickel Plated Graphite (Ni/C)

Electrical Characteristics

Resistance to Petroleum	No
Volume Resistivity (Max)	.05 Ω.cm

Body Features

Gasket Type	Extruded EMI Gasket
Gasket Shape	Tube

Dimensions

Product Length	1 m[3.28 ft]
Outside Diameter	2.6 mm[.102 in]



Inside Diameter	1.1 mm[.043 in]
-----------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 160 °C[-67 – 320 °F]
-----------------------------	----------------------------

Other

Reuse Limits	Reusable More Than 3 Times
--------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # CAT-EMIG-0001

Extruded EMI Gasket Conductive Strip



TE Part # 2452658-1

SNA Tube 2.6mm OD x 1.1mm ID x 1m L

Also in the Series | **Kemtron 1202 Series**




EMI Gaskets(36)

Customers Also Bought



TE Part #SP2-50

STRING POT 50 INCH RANGE



TE Part #206322-9

CABLE CLAMP SIZE 17



TE Part #211398-1

Cable/Panel Mount Connector, CPC Series 1



TE Part #66504-3

20 DF SCKT CONT



TE Part #1-1393143-9

27E166=SOCKET,KH,14,SCW,PLES



TE Part #2420753-1

Extruded EMI Gasket Conductive Strip



TE Part #NB14134001

VERSAFIT-1/2-0-SP



TE Part #91124-1

EXTRACTION TOOL

Documents

Product Drawings

SNG Tube 2.6mm OD x 1.1mm ID x 1m L

English

Datasheets & Catalog Pages

Performance Materials brochure

English



Datasheet - Conductive Elastomers

English

Product Specifications

Application Specification

English