




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**  
Connector & Housing Type: **Plug, Receptacle**  
Connector System: **Wire-to-Panel, Wire-to-Wire**  
Number of Positions: **2**  
Centerline (Pitch): **7.92 mm [.312 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug, Receptacle
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Number of Positions	2
Number of Power Positions	2
Number of Signal Positions	0
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features



Contact Current Rating (Max)	53 A
Contact Retention Within Housing	With
Contact Type	Blade

Termination Features

Termination Method to Wire & Cable	Crimp & Solder
------------------------------------	----------------

Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	7.92 mm[.312 in]
Housing Material	Nylon

Dimensions

Connector Height	7.92 mm[.312 in]
Product Width	28.55 mm[1.124 in]
Product Length	24.51 mm[.965 in]
Wire Size	10 – 6 AWG

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards


CSA Rating	Certified, LR 7189
UL Rating	Recognized
Agency/Standard	CSA, UL
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	200
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 54489-2  
HSG ASSY,PWR LK,SRS1,2POS,FLNG

Customers Also Bought




TE Part #6134370001  
RPS-22-18/2.0-9



TE Part #1-1478762-5  
METAL BACKSHELL 15 WAY TOP E



TE Part #1-1478763-5  
METAL BACKSHELL 15 WAY 45 DE



TE Part #5745563-3  
HD KIT,SCREWLOCK





TE Part #324955  
TERMINAL,SOLIS R 16-14 8




TE Part #556137-2  
HSG,AMPINERGY WTW,1 POS, BLACK



TE Part #770026-1  
04P UMNLI IN-LINE CAP HSG KIT



TE Part #770017-1  
02P UMNLI IN-LNE PLUG HSG KIT



TE Part #53892-4  
CONTACT,PWR LK,SRS1,LS PC,CRMP

Documents

Product Drawings

HSG ASSY,PWR LK,SRS1,2POS,FLNG

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_54489-2\_L.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_54489-2\_L.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_54489-2\_L.3d\_stp.zip

English

3D PDF

English

Customer View Model

ENG\_CVM\_54489-2\_E.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_54489-2\_E.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_54489-2\_E.3d\_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

Japanese

Power-Lock 75 Series Contacts

Japanese

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

Agency Approval Document

English