



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **6.35 mm [.25 in]**

Features

Product Type Features

Rectangular Power Connector Type	Header
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	2
PCB Mount Orientation	Vertical
Number of Power Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Multiple Contact Types	Without
------------------------	---------



PCB Contact Termination Area Plating Material Thickness	2.54 μm[100 μin]
Contact Layout	Inline
Contact Underplating Material Thickness	1.27 μm[50 μin]
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	12 A
Contact Retention Within Housing	Without
Contact Type	Pin
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	.76 – .91 μm[30 – 36 μin]

Termination Features

Termination Post & Tail Length	3.05 mm[.12 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Strain Relief	Without
Mating Alignment Type	Polarization
Mating Retention	With
Mating Alignment	With
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Positive Lock
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	6.35 mm[.25 in]
Housing Color	Natural
Housing Material	Nylon

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------



Industry Standards

UL Rating	Recognized
Agency/Standard	UL, VDE
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 640713-1 02P UMNL STR/REL & INSERT	 TE Part # 1-350589-0 STR/REL CLAMP NATL	 TE Part # 350811-1 STR/REL CLAMP	 TE Part # 640713-2 02P UMNL STR/RELIEVE
 TE Part # 1-480698-0 02P UMNL PLUG HSG NATL	 TE Part # 794269-1 02P UMNL INTERFACE SEAL	 TE Part # 794815-1 02P UMNL CAP HSG, HI TEMP	 TE Part # 1703062-1 CAP, 2 CIRCUIT, UNIVERSAL MATE-N-LOK
 TE Part # 794991-1 02P UMNL BLACK INTERFACE SEAL	 TE Part # 1586856-1 02P UMNL CAP HSG, GW	 TE Part # 350848-2 02P UMNL PLUG TEST ASSY 94VO	 TE Part # 1-640719-1 02P UMNL STR/REL NATL
 TE Part # 794270-1 02P UMNL WIRE SEAL	 TE Part # 1-640719-0 02P UMNL STR/REL & INSRT NATL	 TE Part # 643250-1 02P UMNL ASSY MOD HSG V0	 TE Part # 1703062-2 CAP, 2 CIRCUIT, UNIVERSAL MATE-N-LOK
 TE Part # 1703062-3 CAP, 2 CIRCUIT, UNIVERSAL MATE-N-LOK	 TE Part # 2-480699-0 02P UMNL CAP HSG NATL	 TE Part # 2178649-1 2P UMNL CAP HSG, GW	 TE Part # 2178649-2 2P UMNL CAP HSG, GW

Also in the Series | [Universal MATE-N-LOK](#)



Circular Power Connectors(2)



Connector Contacts(2)




Connector Seals & Cavity Plugs(27)



Connector Strain Relief(34)



Insertion & Extraction Tools(4)



Power Contacts(207)



Rectangular Connector Adapters(7)



Rectangular Connector Hardware(1)



Rectangular Connector Housings(1)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(8)



Rectangular Power Connectors(672)

Customers Also Bought



TE Part #T4111501041-000
M12,MALE,STRAIGHT,D CODE,4P, PG7,GOLD



TE Part #2-748003-0
09 PLUG SP/FMS BRDLK



TE Part #5-146257-8
16 MODII HDR DRST B/A .100CL L



TE Part #1676363-2
RN 0805 4K99 0.1% 10PPM 1KRL



TE Part #5-104550-4
30 SYS50 SURFMNT DRST RCPT LF



TE Part #5-1618241-6
K81C235=RELAY, VACUUM, SPDT



TE Part #4515-DS5A005DP
PRESS XDCR,ANALOG,INH20 RANGE



TE Part #NB19162001
RNF-100-1/8-BK-STK



Documents

Product Drawings

02P UMNL PIN HDR ASSY V2 LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_350582-4_Z.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_350582-4_Z.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_350582-4_Z.3d_stp.zip

English

Customer View Model

ENG_CVM_350582-4_T.3d_igs.zip

English

Customer View Model

ENG_CVM_350582-4_T.3d_stp.zip

English

Customer View Model

ENG_CVM_350582-4_T.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Product Specifications

Application Specification

English



Product Environmental Compliance

TE Material Declaration

English