



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Connector System: **Wire-to-Board**
Number of Positions: **14**
Centerline (Pitch): **2.54 mm [.1 in]**
PCB Mount Retention: **Without**
PCB Mount Orientation: **Vertical**

Features

Product Type Features

Ribbon Cable Connector Header Type	Pin Header
Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	14
PCB Mount Orientation	Vertical
Number of Rows	2

Electrical Characteristics

Insulation Resistance	5000 MΩ
Operating Voltage	250 VAC

Body Features

Daisy Chain	Without
-------------	---------



Primary Product Color	Black
Connector Profile	Low

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
Mating Pin Diameter	.64 mm[.025 in]
Contact Type	Socket
Wire Contact Termination Area Plating Thickness	1.27 µm[50 µin]
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	.76 µm[29.92 µin]
Contact Mating Area Plating Material	Gold, Gold Flash over Palladium Nickel
Contact Shape & Form	Tuning Fork
Contact Underplating Material	Nickel
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Mating Alignment	With
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Alignment Type	Polarization
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Connector Length	22.35 mm[.88 in]
Connector Height	15.16 mm[.597 in]
Connector Width	7.49 mm[.295 in]



Wire Size	.08 – .15 mm ²
Compatible Insulation Diameter Range	.79 – .94 mm[.031 – .037 in]
Row-to-Row Spacing	2.54 mm[.1 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Rating	Recognized
Agency/Standard	CSA, UL
Approved Standards	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	50
Packaging Method	Box & Tube, Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-AM74-UN384H AMP-LATCH UNIVERSAL HEADERS	 TE Part # 499252-9 014 STRAIN RELIEF A-L RCPT	 TE Part # 5103309-2 A/L LOW PRO HDR 14P VERT BLACK	 TE Part # 5103310-2 A/L LOW PRO HDR 14P RA BLACK
 TE Part # 1-111446-5 14 UNIV I/O, NO EARS, LEAD FREE	 TE Part # 5103308-2 A/L LOW PRO HDR 14P VERT BLACK	 TE Part # 5103311-2 A/L LOW PRO HDR 14P RA BLACK	 TE Part # 5104338-2 A/L LOW PRO HDR 14P VERT HT
 TE Part # 1-111492-6 014 UNIV I/O 30DP NO EARS LTCH	 TE Part # 1-111504-5 014 UNIV I/O 30DP NO EARS LTCH	 TE Part # 5104340-2 A/L LOW PRO HDR 14P RA HT	 TE Part # 768340-1 UNIV HAND TOOL KIT AMPLATCH

Also in the Series | AMP-LATCH - NOVO



Ribbon Cable Connectors(46)

Customers Also Bought



TE Part #1-1609117-6
6EHG8-2=F8291

TE Part #1658537-1
SOCKET CONT DUPL PLT STRIP HD-

TE Part #1658539-2
PIN CONT DUPL PLT STRIP HD-20

TE Part #2035363-4
1X6 GENERATION Y ASSY KEYC CPA

TE Part #5788816-1
RCPT ASSY,26P,HDP-22,CN

TE Part #2309644-1
MQS, CONNECTOR HOUSING

TE Part #NB18784001
RNF-100-1/16-CL-SP

TE Part #1210334001
MT5000-3/16-0-SP

TE Part #0662694002
MT2000-6.0-X-SP

Documents

Product Drawings
014 NOVO DUAL 30DP FT
English

CAD Files
Customer View Model
ENG_CVM_CVM_1658624-2_D.2d_dxf.zip
English
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1658624-2_D.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1658624-2_D.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



Ribbon Cable Interconnect Solutions

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

Agency Approval Document

English