

5-2213222-1 ✓ ACTIVE

NECTOR | NECTOR S

TE Internal #: 5-2213222-1

Plug & Socket Lighting Connector Accessories, Bus Bar, Wire-to-Bus Bar, 2 Position, Bus Bar, 125 VAC, NECTOR S

[View on TE.com >](#)



Connectors > Lighting Connectors > Plug & Socket Lighting Connector Accessories



Lighting Connector Accessory Type: **Bus Bar**

Connector System: **Wire-to-Bus Bar**

Number of Positions: **2**

Centerline (Pitch): **3.6 mm**

Sealable: **No**

Features

Product Type Features

Lighting Connector Accessory Type	Bus Bar
Connector System	Wire-to-Bus Bar
Sealable	No
Connector & Contact Terminates To	Bus Bar

Configuration Features

Keying Arrangement	HV-3
Number of Positions	2

Electrical Characteristics

Operating Voltage	125 VAC
-------------------	---------

Body Features

Primary Product Color	White
-----------------------	-------

Contact Features

Contact Current Rating (Max)	6 A
------------------------------	-----

Mechanical Attachment

Connector Mounting Type

Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)

3.6 mm

Operation/Application

Circuit Application

Power

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023
(235)Candidate List Declared Against: JUNE
2023 (235)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900
ppm.


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 5-2213222-5
NECTOR S BUS BAR US, THRU HV-4


Also in the Series | **NECTOR S**




Insertion & Extraction Tools(3)



Lighting Cable Assemblies(1)



Plug & Socket Lighting Connector Accessories(57)



Plug & Socket Lighting Connectors(54)

Customers Also Bought



TE Part #1-2213222-1
NECTOR S BUS BAR SEALED US,
THRU HV-3



TE Part #293270-3
NECTOR S BUS BAR SEALED CONN
HV-1

Documents

Product Drawings

[NECTOR S BUS BAR US, THRU HV-3](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_5-2213222-1_B.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_5-2213222-1_B.3d_igs.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_5-2213222-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
[NECTOR_S_LINE_CONNECTOR_BROCHURE](#)

English

Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English