

2120432-3

✓ ACTIVE

MotorMan

TE Internal #: 2120432-3

Crimp Sleeve, UL 94V-0, MotorMan

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Crimp Sleeve**

UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Strain Relief Accessory Type

Crimp Sleeve

Industry Standards

UL Flammability Rating

UL 94V-0

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)

Candidate List Declared Against: JUNE 2023 (235)

SVHC > Threshold:

Pb (3.7% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2083288-2

Also in the Series | MotorMan



Circular Connector Caps & Covers(1)



Circular Connector Contact Inserts(2)



Connector Seals & Cavity Plugs(2)



Connector Strain Relief(3)



Rectangular Caps & Covers(1)




Rectangular Connector Hardware(2)



Rectangular Connector Hoods & Bases(4)



Rectangular Connector Locking(2)




Rectangular Contact Inserts(5)



Rectangular Power Connectors(2)

Customers Also Bought

TE Part #2120338-3
SCREEN CLAMPTE Part #2120339-1
SIDE CLIPTE Part #2295894-1
SIGNAL HOUSINGTE Part #1103426-1
MALE INSERT, CRIMP, 4-POS. 22DF
CONTACTSTE Part #2120330-1
METAL HOOD / KITTE Part #2120457-1
HOOD KIT MOTORMAN HC 180
METALTE Part #2151338-2
OCEAN-2.0-APPLICATOR-S-
140F140O210OTE Part #184113-1
TERM,COPALUM R 4/0A 3/0C 1/2

Documents

Product Drawings

CRIMP SLEEVE

English

Product Specifications

Product Specification

English