




EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > Multi-Function Inlet, Corcom HG Series



Filter Type: **Power Entry Module**

Filter Switch Type: **No Switch**

Filter Shield Type: **Shielded**

Product Orientation: **Right Angle**

Leakage Current (Max) (120VAC, 60Hz): **2 μ A**

[All Multi-Function Inlet, Corcom HG Series \(11\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Entry Module
Filter Switch Type	No Switch
Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-14

Configuration Features

Fuse Options	Dual
--------------	------

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	2 μ A
Leakage Current (Max) (250VAC, 50Hz)	5 μ A
Current Rating	1 A



Operating Voltage

250 VAC

Body Features

Filter Shield Type	Shielded
Product Orientation	Right Angle

Mechanical Attachment

Panel Mount Feature Type	Flanged
--------------------------	---------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-G34
CORCOM GG SERIES MULTI-FUNCTION INLET FI

TE Part # 1609116-6
10EHGS1-2=F8242

Also in the Series | Corcom HG

Multi-Function Inlet Filters(11)

Customers Also Bought

TE Part #2-6609115-3
6EGG1-2=F7386D

TE Part #206060-1
CPC PLUG ASSEMBLY SIZE 11-4

TE Part #5747844-4
09 MSFL RCPT RA 318 (IN,FM,BL)

TE Part #2-1419104-1
T9AS1D22-24

TE Part #344108-1
36 WAY HEADER WIRE TO BD.FOR E

TE Part #1375819-2
CST-100 II CONTACT 15 GOLD PLT

TE Part #5-87191-2
LOCKING CLIP ASSY .025 SQ LP

TE Part #1676278-2
RN 0805 28K 0.1% 10PPM 1KRL

TE Part #4-1419108-0
RTE24005F



Documents

Product Drawings

1EHG1-2=F7702 S0

English

CAD Files

Customer View Model

ENG_CVM_CVM_6609116-1_E1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6609116-1_E1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_6609116-1_E1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_CORCOM_PRODUCT_GUIDE

English

1654001_CORCOM_PRODUCT_GUIDE_GG_HG

English

Corcom Combined Selector Charts

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English