



Connectors > Circular Connectors > Standard Circular Connectors



Sealable: No

Contact Current Rating (Max): 5 A

Circuit Application: Signal

Shell Base Material: Brass

Circular Connector Shell Size: 15

Features

Product Type Features

Sealable	No
Shell Type	Metal

Body Features

Shell Base Material	Brass
---------------------	-------

Contact Features

Contact Current Rating (Max)	5 A
Circular Connector Contact Type	Pin

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Housing Features

Circular Connector Shell Size	15
-------------------------------	----

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Signal



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Pb (1.5% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


TE Part # C0-0201-000-000
CRIMPING TOOL MID-SIZE

TE Part # C0-0235-000-000
DIGITAL CRIMPING TOOL, SMALL


TE Part # C0-0258-000-000
POSITIONING INSERT FOR 1 MM CONTACTS

Customers Also Bought







TE Part #60-0252-011-000
CONTACT SOCKET 1 MM




TE Part #AGC874N0000150A000
617 RECEPTACLE ANGLED
ROTATABLE




TE Part #BGC906N0000151A000
917 RECEPTACLE, ANGLED,
ROTATABLE




TE Part #BSA861N0085201A000
917 PLUG




TE Part #EDA202N00000501000
915 BULKHEAD CONNECTOR




TE Part #EGA101N00000001000
615/915 YTEC RECEPTACLE, ANGLED




TE Part #EKA201N00330500000
915 EXTENSION



TE Part #EEA201N00000501000
915 ITEC RECEPTACLE



TE Part #EEA201N00000511000
915 itec receptacle



TE Part #EKA001N00310103000
615 EXTENSION

Documents

Product Drawings
CONTACT PIN 1 MM

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_61-0239-011-000_B.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_61-0239-011-000_B.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_61-0239-011-000_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[PIN 1mm 61.239.11](#)

German

[PIN 1mm 61.239.11](#)

English