




Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories



Automotive Connector Accessory Type: **Mounting Clip**
Primary Product Material: **PBT GF**
Primary Product Color: **Yellow**
Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Mounting Clip
-------------------------------------	---------------

Body Features

Primary Product Material	PBT GF
Primary Product Color	Yellow

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC



Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2325102-1
2POS,TAB1.2X0.6,HDR ASSY,180DEG,SLDR




TE Part # 2325106-1
ADAPTER,2POS,1.2X0.6,PIN HSG ASSY


Customers Also Bought




TE Part #2103124-1
HVA280 2P HEADER ASSY, KEY A




TE Part #1587724-3
OUTER FERRULE, SIZE C, HVA280




TE Part #1587985-1
INNER HSG SUBASSY, HVA280-2PHM




TE Part #1587723-3
INNER FERRULE, SIZE C, HVA280




TE Part #2272168-1
MCON WIRE DRESS, 2P PLUG, STRAIGHT



TE Part #DRC16-24SAE
PLG, 24P, BLK, E, A



TE Part #4-2103015-1
PLUG SUBASSY, A, HVA280-2PHM F



TE Part #2103154-1
CABLE SEAL, SIZE 1, HVA280



Documents

Product Drawings

MNTG CLIP,ENETSEAL PLUS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2325098-6_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2325098-6_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2325098-6_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English