

## FEATURES AND BENEFITS

- Drives 6 N-channel MOSFETs
- Synchronous rectification for low power dissipation
- Internal UVLO and thermal shutdown circuitry
- Hall element inputs
- PWM current limiting
- Dead time protection
- FG outputs
- Standby mode
- Lock detect protection
- Overvoltage protection

## PACKAGE: 28-contact QFN (ET package)



Not to scale

## DESCRIPTION

The A4931 is a complete 3-phase brushless DC motor pre-driver. The device is capable of driving a wide range of N-channel power MOSFETs and can support motor supply voltages up to 30 V. Commutation logic is determined by three Hall-element inputs spaced at 120°.

Other features include fixed off-time pulse-width modulation (PWM) current control for limiting inrush current, locked-rotor protection with adjustable delay, thermal shutdown, overvoltage monitor, and synchronous rectification. Internal synchronous rectification reduces power dissipation by turning on the appropriate MOSFETs during current decay, thus shorting the body diode with the low  $R_{DS(on)}$  MOSFET. Overvoltage protection disables synchronous rectification when the motor pumps the supply voltage beyond the overvoltage threshold during current recirculation.

The A4931 offers enable, direction, and brake inputs that can control current using either phase or enable chopping. Logic outputs FG1 and FG2 can be used to accurately measure motor rotation. Output signals toggle state during Hall transitions, providing an accurate speed output to a microcontroller or speed control circuit.

The A4931 is supplied in a 5 mm  $\times$  5 mm, 28-terminal QFN package with exposed thermal pad. This small footprint package is lead (Pb) free with 100% matte-tin leadframe plating.



## **Typical Application**

#### **SELECTION GUIDE**

Part Number	Packing	Package	Operating Ambient Temperature, T <sub>A</sub> (°C)		
A4931METTR-T	1500 pieces per reel	5 mm × 5 mm, 0.90 mm nominal height QFN	–20 to 105		
A4931GETTR-T	1500 pieces per reel	5 mm × 5 mm, 0.90 mm nominal height QFN	–40 to 105		

#### **ABSOLUTE MAXIMUM RATINGS**

Characteristic Symbol Notes		Notes	Rating	Units
Load Supply Voltage	V <sub>BB</sub>		38	V
Motor Phase Output	S <sub>X</sub>	t <sub>w</sub> < 500 ns	-3	V
Hall Input	V <sub>Hx</sub>	DC	-0.3 to 7	V
Logic Input Voltage Range	V <sub>IN</sub>		-0.3 to 7	V
Logic Output Voltage Range	V <sub>FG</sub>	FG1, FG2 pins	-0.3 to 7	V
Operating Ambient Temperature		Range M	-20 to 105	°C
Operating Ambient Temperature	T <sub>A</sub>	Range G	-40 to 105	°C
Maximum Junction Temperature	T <sub>J</sub> (max)		150	°C
Storage Temperature	T <sub>stg</sub>		-40 to 150	°C

#### THERMAL CHARACTERISTICS

Characteristic	Symbol	Rating	Units	
Package Thermal Resistance, Junction to Ambient	R <sub>0JA</sub> 4-layer PCB based on JEDEC standard		32	°C/W
Package Thermal Resistance, Junction to Exposed Pad			2	°C/W

\*For additional information, refer to the Allegro website.



## FUNCTIONAL BLOCK DIAGRAM





## **PINOUT DIAGRAM AND TERMINAL LIST**



ET Package Pinout Diagram

#### **Terminal List**

Number	Name	Description		
1	HA+	Hall input A		
2	HA -	Hall input A		
3	HB+	Hall input B		
4	HB -	Hall input B		
5	HC+	Hall input C		
6	HC-	Hall input C		
7	GND	Ground		
8	HBIAS	Hall bias power supply output		
9	CP1	Charge pump capacitor terminal		
10	CP2	Charge pump capacitor terminal		
11	VBB	Supply voltage		
12	VCP	Reservoir capacitor terminal		
13	SENSE	Sense resistor connection		
14	GLC	Low side gate drive C		

Number	Name	Description
15	GLB	Low side gate drive B
16	GLA	Low side gate drive A
17	GHC	High side gate drive C
18	SC	High side source connection C
19	GHB	High side gate drive B
20	SB	High side source connection B
21	GHA	High side gate drive A
22	SA	High side source connection A
23	FG1	FG 1 speed control output (3 $\Phi$ inputs)
24	FG2	FG 2 speed control output (ΦA input)
25	CLD	Locked rotor detect timing capacitor
26	DIR	Logic input – motor direction
27	ENABLE	Logic input – external PWM control
28	BRAKEZ	Logic input – motor brake (active low)



## **ELECTRICAL CHARACTERISTICS**<sup>\*</sup>: Valid at $T_A$ = 25°C, $V_{BB}$ = 24 V, unless noted otherwise

Characteristics	Symbol	Test Conditions	Min.	Тур.	Max.	Units	
Supply Voltage Range	V <sub>BB</sub>	Operating	8	-	V <sub>BBOV</sub>	V	
Mater Current Current		f <sub>PWM</sub> < 30 kHz, C <sub>LOAD</sub> = 1000 pF	_	5	6	mA	
Motor Supply Current	I <sub>BB</sub>	Charge pump on, outputs disabled, Standby mode	_	3	3.5	mA	
HBIAS Voltage	V <sub>HBIAS</sub>	0 mA ≤ I <sub>HBIAS</sub> ≤ 24 mA	7.2	7.5	7.8	V	
HBIAS Current Limit	I <sub>HBIASlim</sub>		30	-	-	mA	
CONTROL LOGIC		·					
	V <sub>IN(1)</sub>		2	-	_	V	
Logic Input Voltage	V <sub>IN(0)</sub>		-	-	0.8	V	
	I <sub>IN(1)</sub>	V <sub>IN</sub> = 2 V	-1	<1.0	1	μA	
Logic Input Current	I <sub>IN(0)</sub>	V <sub>IN</sub> = 0.8 V	-1	<-1.0	1	μA	
Innut Din Olitak Daiaat		ENB pin	350	500	650	ns	
Input Pin Glitch Reject	t <sub>GLITCH</sub>	DIR, BRAKEZ pins	700	1000	1300	ns	
ENB Standby Pulse Propagation Delay	t <sub>dENB</sub>	To outputs off	2.1	3	3.9	ms	
HBIAS Wake-Up Delay, Standby Mode	t <sub>dHBIAS</sub>	C <sub>HBIAS</sub> = 0.1 µF	_	15	25	μs	
GATE DRIVE							
High-Side Gate Drive Output	V <sub>GS(H)</sub>	Relative to V <sub>BB</sub> , I <sub>GATE</sub> = 2 mA	7		-	V	
Low-Side Gate Drive Output	V <sub>GS(L)</sub>	I <sub>GATE</sub> = 2 mA	7	-	-	V	
Gate Drive Current (Sourcing)	I <sub>Gate</sub>	$V_{GH} = V_{GL} = 4 V$	20	30	-	mA	
Gate Drive Pull Down Resistance	R <sub>Gate</sub>		10	28	40	Ω	
Dead Time	t <sub>dead</sub>		700	1000	1300	ns	
Current Limit Input Threshold	V <sub>REF</sub>		180	200	220	mV	
Fixed Off-Time	t <sub>OFF</sub>		18	25	37	μs	
PROTECTION							
Thermal Shutdown Temperature	T <sub>JTSD</sub>		155	170	185	°C	
Thermal Shutdown Hysteresis	T <sub>JTSDhys</sub>		14	15	26	°C	
VBB UVLO Enable Threshold	V <sub>BBUV</sub>	Rising V <sub>BB</sub>	6.2	7	7.85	V	
VBB UVLO Hysteresis	V <sub>BBUVhys</sub>		0.4	0.75	1	V	
VCP UVLO	V <sub>CPUV</sub>	Relative to V <sub>BB</sub>	4.6	-	6	V	
Lock Detect Duration	t <sub>lock</sub>	C = 0.1 µF	1.5	2	2.5	S	
VBB Overvoltage Threshold	V <sub>BBOV</sub>	Rising V <sub>BB</sub>	30	33	37.5	V	

Continued on the next page...



#### ELECTRICAL CHARACTERISTICS\* (continued): Valid at T<sub>A</sub>= 25°C, V<sub>BB</sub> = 24 V, unless noted otherwise

Characteristics	Symbol	Test Conditions	Min.	Тур.	Max.	Units
HALL LOGIC						
Hall Input Current	I <sub>HALL</sub>	V <sub>IN</sub> = 0.2 to 3.5 V	-1	0	1	μA
Common Mode Input Range	V <sub>CMR</sub>		0.2	-	3.5	V
AC Input Voltage Range	V <sub>HALL</sub>		60	-	-	mV <sub>p-p</sub>
Hall Thresholds	V <sub>th</sub>	Difference between Hall inputs at transitions	-	±10	-	mV
		$T_J = 25^{\circ}C$	10	20	30	mV
Hall Threshold Hysteresis	V <sub>HYS</sub>	$T_J = -20^{\circ}C$ to $125^{\circ}C$	5	20	40	mV
Pulse Reject Filter	t <sub>pulse</sub>		-	2	-	μs
FG						
FG Output Saturation Voltage	V <sub>FG(sat)</sub>	I <sub>FG</sub> = 2 mA	-	-	0.5	V
FG Leakage Current	I <sub>FGlkg</sub>	V <sub>FG</sub> = 5 V	-	-	1	μA

\*Typical data are for initial design estimations only, and assume optimum manufacturing and application conditions. Performance may vary for individual units, within the specified maximum and minimum limits.

For input and output current specifications, negative current is defined as coming out of (sourcing) the specified device pin.

Specifications throughout the allowed operating temperature range are guaranteed by design and characterization.



Conditio	Condition			Resulti	ng Pre-	Driver C	Dutputs		Motor Output						
Conditio	n	HA	HB	HC	BRAKEZ	ENB	GHA	GLA	GHB	GLB	GHC	GLC	Α	В	С
	А	+	-	+	HI	LO	н	LO	LO	HI	LO	LO	HI	LO	Z
	В	+	-	-	HI	LO	н	LO	LO	LO	LO	HI	HI	Z	LO
DIR = 1	С	+	+	-	HI	LO	LO	LO	HI	LO	LO	HI	Z	HI	LO
(Forward)	D	-	+	-	HI	LO	LO	HI	HI	LO	LO	LO	LO	HI	z
	Е	-	+	+	HI	LO	LO	HI	LO	LO	HI	LO	LO	Z	н
	F	-	-	+	HI	LO	LO	LO	LO	HI	HI	LO	Z	LO	н
	А	+	-	+	HI	LO	LO	HI	HI	LO	LO	LO	LO	HI	Z
	F	-	-	+	HI	LO	LO	LO	HI	LO	LO	HI	Z	HI	LO
DIR = 0	Е	-	+	+	HI	LO	н	LO	LO	LO	LO	HI	HI	Z	LO
(Reverse)	D	-	+	-	HI	LO	н	LO	LO	HI	LO	LO	HI	LO	z
	С	+	+	-	HI	LO	LO	LO	LO	HI	HI	LO	Z	LO	н
	В	+	-	-	HI	LO	LO	HI	LO	LO	HI	LO	LO	Z	н
Fault*		+	+	+	HI	Х	LO	LO	LO	LO	LO	LO	Z	Z	Z
Fault*		-	-	-	HI	х	LO	LO	LO	LO	LO	LO	Z	Z	z
Brake*		Х	Х	Х	LO	Х	LO	HI	LO	HI	LO	HI	LO	LO	LO

#### Logic States Table (See timing charts, below) X = Don't Care, Z = high impedance

\* DIR = Don't Care









Figure 2: Power-Down Timing Diagram



## FUNCTIONAL DESCRIPTION

### **Current Regulation**

Load current is regulated by an internal fixed off-time PWM control circuit. When the outputs of the full bridge are turned on, current increases in the motor winding until it reaches a value,  $I_{TRIP}$ , given by:

$$I_{\text{TRIP}} = 200 \text{ mV} / R_{\text{SENSE}}$$

When  $I_{TRIP}$  is reached, the sense comparator resets the source enable latch, turning off the source driver. At this point, load inductance causes the current to recirculate for the fixed off-time period.

#### **Enable Logic**

The Enable input terminal (ENB pin) allows external PWM. ENB low turns on the selected sink-source pair. ENB high switches off the appropriate drivers and the load current decays. If ENB is held low, the current will rise until it reaches the level set by the internal current control circuit. Typically PWM frequency is in 20 to 30 kHz range. If the ENB high pulse width exceeds 3 ms, the gate outputs are disabled. The Enable logic is summarized in the following table:

ENB Pin Setting	Outputs	Outputs State
0	On	Drive
1	Source Chopped	Slow Decay with Synchronous Rectification
1 for > 3 ms typical	Off	Disable

## **Fixed Off-Time**

The A4931 fixed off-time is set to 25  $\mu$ s nominal.

### **PWM Blank Timer**

When a source driver turns on, a current spike occurs due to the reverse recovery currents of the clamp diodes as well as switching transients related to distributed capacitance in the load. To prevent this current spike from erroneously resetting the source Enable latch, the sense comparator is blanked. The blanking timer runs after the off-time counter completes, in order to provide the blanking function. The blanking timer is reset when ENB is chopped or DIR is changed. With external PWM control, a DIR change or an ENB on triggers the blanking function. The duration is fixed at  $1.5 \,\mu$ s.

### **Synchronous Rectification**

When a PWM-off cycle is triggered, either by a chop command on ENB or by an internal fixed off-time cycle, load current recirculates. The A4931 synchronous rectification feature turns on the appropriate MOSFETs during the current decay, and effectively shorts out the body diodes with the low  $R_{DS(on)}$  driver. This lowers power dissipation significantly and can eliminate the need for external Schottky diodes.

#### Brake Mode

A logic low on the BRAKEZ pin activates Brake mode. A logic high allows normal operation. Braking turns on all three sink drivers, effectively shorting out the motor-generated BEMF. The BRAKEZ input overrides the ENB input and also the Lock Detect function.

It is important to note that the internal PWM current control circuit does not limit the current when braking, because the current does not flow through the sense resistor. The maximum current can be approximated by  $V_{BEMF} / R_{LOAD}$ . Care should be taken to insure that the maximum ratings of the A4391 are not exceeded in the worse case braking situation, high speed and high inertial load.

### **HBIAS** Function

This function provides a power supply of 7.5 V, current-limited to 30 mA. This reference voltage is used to power the logic sections of the IC and also to power the external Hall elements.

### Standby Mode

To prevent excessive power dissipation due to the current draw of the external Hall elements, Standby mode turns off the HBIAS output voltage. Standby mode is triggered by holding ENB high for longer than 3 ms. Note that Brake mode overrides Standby mode, so hold the BRAKEZ pin high in order to enter Standby mode.

### Charge Pump

The internal charge pump is used to generate a supply above  $\rm V_{BB}$  to drive the high-side MOSFETs. The voltage on the VCP pin is internally monitored, and in case of a fault condition, the outputs of the device are disabled.



### Fault Shutdown

In the event of a fault due to excessive junction temperature or due to low voltage on VCP or VBB, the outputs of the device are disabled until the fault condition is removed. At power-up, the UVLO circuit disables the drivers.

#### **Overvoltage Protection**

VBB is monitored to determine if a hazardous voltage is present due to the motor generator pumping up the supply bus. When the voltage exceeds  $V_{BBOV}$ , the synchronous rectification feature is disabled.

#### **Overtemperature Protection**

If die temperature exceeds approximately 170°C, the Thermal Shutdown function will disable the outputs until the internal temperature falls below the 15°C hysteresis.

#### Hall State Reporting

The FG1 pin is an open-drain output that changes state at each transition of an external Hall element. The FG2 pin is an opendrain output that changes state at each HAx transition.

#### **Lock Detect Function**

The IC will evaluate a locked rotor condition under either of these two different conditions:

• The FG1 signal is not consistently changing.

• The proper commutation sequence is not being followed. The motor can be locked in a condition in which it toggles between two specific Hall device states.

Both of these fault conditions are allowed to persist for period of time,  $t_{lock}$ .  $t_{lock}$  is set by capacitor connected to CLD pin.  $C_{LD}$  produces a triangle waveform (1.67 V peak-to-peak) with frequency linearly related to the capacitor value.  $t_{lock}$  is defined as 127 cycles of this triangle waveform, or:

$$t_{\rm lock} = C_{\rm LD} \times 20 \text{ s/}\mu\text{F}$$

After the wait time,  $t_{lock}$ , has expired, the outputs are disabled, and the fault is latched. These fault conditions can only be cleared by any one of the following actions:

- Rising or falling edge on the DIR pin
- VBB UVLO threshold exceeded (during power-up cycle)
- ENB pin held high for  $> t_{lock} / 2$

The Lock Detect function can be disabled by connecting CLD to GND.

When the A4931 is in Brake mode, the Lock Detect counter is disabled.



ET Package, 28-Contact QFN



Coplanarity includes exposed thermal pad and terminals

EIA/JEDEC Standard JESD51-5)

Branding scale and appearance at supplier discretion



#### **Revision History**

Number	Date	Description		
8	February 10, 2020 Added G temperature rated part option; minor editorial updates			
9	9 February 10, 2022 Updated package drawing (page 11)			

Copyright 2022, Allegro MicroSystems.

Allegro MicroSystems reserves the right to make, from time to time, such departures from the detail specifications as may be required to permit improvements in the performance, reliability, or manufacturability of its products. Before placing an order, the user is cautioned to verify that the information being relied upon is current.

Allegro's products are not to be used in any devices or systems, including but not limited to life support devices or systems, in which a failure of Allegro's product can reasonably be expected to cause bodily harm.

The information included herein is believed to be accurate and reliable. However, Allegro MicroSystems assumes no responsibility for its use; nor for any infringement of patents or other rights of third parties which may result from its use.

Copies of this document are considered uncontrolled documents.

For the latest version of this document, visit our website:

www.allegromicro.com

