



Connectors > Lighting Connectors > Street Lighting Controls > ANSI Street Lighting Receptacles



Lighting Product Type: **Accessory**

Operating Temperature Range: **-40 – 85 °C [-40 – 185 °F]**

Features

Product Type Features

Lighting Product Type	Accessory
-----------------------	-----------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Industry Standards

Agency/Standard	ANSI
-----------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 2359482-1  
LUMAWISE ENDURANCE N+ 7P Base  
With Vent




TE Part # 2359482-2  
LUMAWISE ENDURANCE N+ 7P Base




TE Part # 2359482-3  
LUMAWISE ENDURANCE N+ 5P Base  
With Vent



TE Part # 2359482-4  
LUMAWISE ENDURANCE N+ 5P Base



TE Part # 2359482-5  
LUMAWISE ENDURANCE N+ 3P Base  
With Vent



TE Part # 2359482-6  
LUMAWISE ENDURANCE N+ 3P Base

Customers Also Bought



TE Part #794610-1  
MICRO MNL RPT CNT,LS PC,TIN



TE Part #3-640599-4  
04P MTA156 CONN ASSY 18AWG  
ORA



TE Part #2359482-1  
LUMAWISE ENDURANCE N+ 7P Base  
With Vent

Documents

Product Drawings  
LUMAWISE ENDURANCE N+ Clear Short Dome  
English



CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_2359615-5\\_A1.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2359615-5\\_A1.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2359615-5\\_A1.2d\\_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[LUMAWISE ENDURANCE N+ Network Lighting Controls](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL\\_CERT\\_CB\\_4789600659\\_TR\\_C1](#)

English

[UL\\_CERT\\_CB\\_US\\_37285\\_C1](#)

English