IEC Appliance Outlet F or H, Screw-on Mounting, Front Side, Solder, PCB or Quick-connect Terminal







Flange with countersunk holes





See below:

Approvals and Compliances

Description

- Panel mount :
- Screw-on mounting, front side
- Connector , Pin temperature 70 $^{\circ}\text{C}$
- protection class I or II
- Solder / Quick Connect / PCB Terminal

Weblinks

pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Accessories, Detailed request for product

Technical Data

| 10 A / 250 VAC; 50 Hz |
|---|
| 15 A / 250 VAC; 60 Hz |
| > 4 kVAC between L-N |
| > 2 kVAC between L/N-PE |
| (1 min/50 Hz) |
| -25 °C to 70 °C |
| |
| front side IP20 acc. to IEC 60529 |
| Suitable for appliances with protection |
| class I or II acc. to IEC 61140 |
| Solder / Quick Connect / PCB Terminal |
| in line with PIN-axis |
| PA6, black or grey, UL 94V-0 |
| |

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: 5091

| Approval Logo | Certificates | Certification Body | Description |
|-----------------|---------------|--------------------|------------------------------|
| 10 | VDE Approvals | VDE | Certificate Number: 40034887 |
| c FL °us | UL Approvals | UL | UR File Number: E103791 |

Product standards

Product standards that are referenced

| | Organization | Design | Standard | Description |
|---|--------------|-----------------------|-------------|---|
| | EC | Designed according to | IEC 60320-1 | Appliance couplers for household and similar general purposes |
| | EC | Designed according to | IEC 60320-1 | Appliance couplers for household and similar general purposes |
| (| (UL) | Designed according to | UL 60320-1 | Standard for Attachment Plugs and Receptacles |

Application standards

Application standards where the product can be used


| Organization | Design | Standard | Description |
|--------------|--------------------------------|----------------|---|
| <u>IEC</u> | Suitable for applications acc. | IEC/UL 62368-1 | Audio/video, information and communication technology equipment - Part 1: Safety requirements |

Compliances


The product complies with following Guide Lines

| | g . | | |
|----------------|--------------------------------|-------------|---|
| Identification | Details | Initiator | Description |
| C€ | CE declaration of conformity | SCHURTER AG | The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008. |
| UK CA | UKCA declaration of conformity | SCHURTER AG | The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008. |
| RoHS | RoHS | SCHURTER AG | Directive RoHS 2011/65/EU, Amendment (EU) 2015/863 |
| © | China RoHS | SCHURTER AG | The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS. |
| REACH | REACH | SCHURTER AG | On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force. |

Dimensions [mm]



Flange with countersunk holes




Flange with through holes special type

Config. Code

5091 - H - A B C 0- D - E

The characters are placeholders for the correspondingly keys of selections from the key tables.



All Variants

| Туре | Terminals L / N | Terminal Ground | Color | Style | Features | Config. Code | Order Number |
|--------------------|---|---|-------|---|----------|-----------------|--------------|
| Protection class I | solder terminal | solder terminal | black | Flange with countersunk holes | - | 5091-X-1110-A-1 | 6182.0001 |
| Protection class I | solder terminal | solder terminal | grey | Flange with countersunk holes | - | 5091-X-1110-B-1 | 6182.0002 |
| Protection class I | PCB-terminal (standard) | PCB-terminal (standard) | black | Flange with through holes special type | - | 5091-X-4440-A-7 | 6182.0004 |
| Protection class I | PCB-terminal (standard) | PCB-terminal (standard) | grey | Flange with through holes special type | - | 5091-X-4440-B-7 | 6182.0005 |
| Protection class I | Quick connect terminal (6.3 x 0.8 mm) | Quick connect terminal (6.3 x 0.8 mm) | black | Flange with countersunk holes | - | 5091-X-9990-A-1 | 6182.0006 |
| Protection class I | Quick connect terminal (6.3 x 0.8 mm) | Quick connect terminal (6.3 x 0.8 mm) | grey | Flange with countersunk holes | - | 5091-X-9990-B-1 | 6182.0008 |

The listed variants should be available from stock. Other versions on request www.schurter.com/contact

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

| Packa | |
|-------|--|
| | |
| | |

100 Pcs

Mating Inlets/Plugs

Category / Description

» Overview complete



| IEC Appliance Inlet C14 with Line Switch 1-pole | KEB1 |
|--|--------|
| IEC Appliance Inlet C14, with Line Switch 2-pole, Voltage Selector and Fuseholder 1or 2-pole | 6766 |
| IEC Appliance Inlet C14 with Line Switch 1- or 2-pole | 6010-K |
| IEC Appliance Inlet C14 with Fuseholder 2-pole, Line Switch 2-pole and Voltage Selector | GRM1 |
| IEC Appliance Inlet C14 with Appliance Outlet F, Line Switch 2-pole and Voltage Selector | PMM |
| | |

Appliance Inlet Overview complete



| 6061, Mounting: Screw, Appliance Inlet: IEC C14 | 6080 |
|--|------|
| 6130, Mounting: Snap-in, Appliance Inlet, IEC C14, For PCB mounting, IP30, Meets the glow wire test acc. IEC 60335-1 edition 4, 7/7.3, Suitable for appliances with protection class I | 6130 |
| G-Stecker, Mounting: Appliance Inlet: IEC C14 Without fuse holder | 6150 |
| 6010, Mounting: Snap-in, Solder / quick-connect / screw / PCB, Appliance Inlet: IEC C14 | 6010 |
| 0711, Mounting: Snap-in, 0.8 mm, Solder, Appliance Inlet: IEC C14 | 0711 |

Distribution Unit Overview complete



| 0712-PQ, Mounting: Snap-in, Front Side, Solder terminal (4.8 x 0.8 mm), 1x Appliance Outlet: IEC F | 0712 | |
|--|------|--|
| 4741, Mounting: 2x Appliance Outlet: IEC F | 4741 | |
| 4747, Mounting: 4x Appliance Outlet: IEC F | 4747 | |
| 4740, Mounting: 6x Appliance Outlet: IEC F | 4740 | |


IEC Inlet Filter Overview complete



| GRF2, Mounting: Rear Side, With EMC-shield and without line filter, 10 A, Plug Connector, Appliance Inlet: IEC C14, Suitable for appliances with protection class I | GRF2 |
|---|------|
| 5110, Mounting: Screw, Front Side, Filter: Standard and Medical Version, Without fuse holder: 10 A, Thermoplastic Appliance Inlet: IEC C14, prewired, Suitable for appliances with protection class I | 5110 |
| KFS, Mounting: Screw, Front Side, Filter: Standard version, Without fuse holder: 10 A, Appliance Inlet: IEC C14, pre- wired | KFS |

Category / Description

Power Entry Module Overview complete



DF11, Mounting: Screw, Rocker switch: non-illuminated or illuminated 2-pole, Quick connect terminals 6.3×0.8 mm, Appliance Inlet: IEC C14, Without fuse holder: Suitable for appliances with protection class I or II 0 DF11, Mounting:Screw, Quick connect terminals 6.3 x 0.8 mm, Without fuse holder: Rocker switch, non-illuminated or illuminated, 2-pole, Appliance Inlet: IEC C14, 250 VAC, prewired, Suitable for appliances with protection class I or II 0 DF11, Power Entry ModuleC14, 55°C, version: L: N: ground: : fuseholder: color: design: dimension S: features: 0 DF11, Moun- DF11 $ting: Snap-in/screw-on, Appliance\ Inlet:\ IEC\ C14, Without\ fuse\ holder::\ black,\ Suitable\ for\ appliances\ with\ protection$ $class\ I\ or\ II\ 0\ DF11, Mounting: Snap-in/screw-on8\ mm,\ Quick\ connect\ terminals\ 6.3\ x\ 0.8\ mm,\ IP40,:\ black,\ Appliance$ Inlet: IEC C14, Circuit Breakers TA45, A, non-illuminated, Protection Class I or II 0 DF11, Mounting: Snap-in/screw-on, mm, Without fuse holder: : IEC Suitable for appliances with protection class I or II 0

DD11, Mounting: Screw-on mounting, Rocker switch: non-illuminated or illuminated 2-pole, Quick connect terminals 4.8 x 0.8 mm, Appliance Inlet: IEC C14, With or without protection cover, Fuseholder: 1-/2-pole, Suitable for appliances DD11 with protection class I

 $DD21, Mounting: Screw-on\ mounting\ Rear\ Side, Rocker\ switch: non-illuminated\ or\ illuminated\ 2-pole, additional\ quick$ connect 4.8 x 0.8 mm Appliance Inlet: IEC C14, Fuseholder: 1-/2-pole

DC11, Mounting: Screw, Rocker switch: non-illuminated or illuminated 1-/2-pole, Quick connect terminals 4.8×0.8 mm, Appliance Inlet: IEC C14, Without fuse holder: Suitable for appliances with protection class I or II

KEB2, Mounting:Screw, Quick connect terminals 4.8 x 0.8 mm, Without fuse holder: Rocker switch, non-illuminated or illuminated, 2-pole, Appliance Inlet: IEC C14, 250 VAC, prewired, Suitable for appliances with protection class I

Power Entry Module with line filter Overview complete



DG12, Mounting: Screw, 8 mm, 15 A, prewired, Standard and Medical Version, Appliance Inlet: IEC C14 C18, Circuit DG12 Breakers TA35: DG12, Suitable for appliances with protection class I or II DD14, Mounting: Screw-on mounting, Front Side, Filter, Standard and Medical Version, Fuseholder:1-/2-pole, 10 A, DD14 Rocker switch: 2-pole, non-illuminated Appliance Inlet: IEC C14, prewired

DD12, Mounting: Screw-on mounting, Front Side, Filter, Standard and Medical Version, Fuseholder:1-/2-pole, 10 A, Rocker switch: 2-pole, non-illuminated Appliance Inlet: IEC C14, prewired KFB1, Mounting: Screw, Front Side, Filter: Standard version, Without fuse holder: 10 A, Rocker switch: 1-pole, Appli-

ance Inlet: IEC C14, prewired KFB2, Mounting: Screw, Front Side, Filter: Standard and Medical Version, Without fuse holder: 10 A, Rocker switch: 2-pole, Appliance Inlet: IEC C14, prewired

DD12

KFB1

KFB2

DC11

KEB2

