




Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Keying



Connector Keying Accessory Type: **Keying Plug**  
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Connector Keying Accessory Type	Keying Plug
---------------------------------	-------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 583680-1 HSG AMP LEAF 15 POS	 TE Part # 583545-1 CONN AMP LEAF 156 C/L 15 POS	 TE Part # 583722-1 HSG AMP LEAF 6 POS	 TE Part # 1-582147-4 15 DUAL AMPLEAF HSG
 TE Part # 1-582147-6 15 DUAL AMPLEAF HSG	 TE Part # 480110-2 HSG AMP LEAF 15 POS	 TE Part # 480110-4 15 DUAL AMP LEAF HSG	 TE Part # 480110-5 HSG AMP LEAF 15 POS
 TE Part # 480110-6 15 DUAL AMP LEAF HSG	 TE Part # 480133-4 18 DUAL AMPLEAF HSG	 TE Part # 480142-3 HSG AMP LEAF 22 POS	 TE Part # 480142-4 22 POS AMP LEAF HSG
 TE Part # 480142-5 22 POS AMP LEAF HSG	 TE Part # 582500-4 15 POS. DUAL AMP LEAF HSG.	 TE Part # 582500-6 15 DUAL AMPLEAF HSG	 TE Part # 583552-2 AMP LEAF 36 POS



TE Part # 583680-2  
AMP LEAF 15 POS



TE Part # 583685-2  
AMP LEAF 30 POS



TE Part # 583722-2  
AMP LEAF 6 POS



TE Part # 583723-2  
HSG AMP LEAF 10 POS

Customers Also Bought




TE Part #1-5747301-6  
37 RCPT SP/FMS SCRLK



TE Part #32837  
PIDG R 22-16 COMM 22-18 MIL 10



TE Part #1-2176071-2  
3521 390K 1% 2W



TE Part #807567-000  
301A022-4/42-0




TE Part #6-1393252-1  
W67-X2Q12-30=M6/M7/M9/W6/W7



TE Part #1-6609032-9  
20VR6=F7312 S0



TE Part #MS583702BA01-50  
MS5837-02BA01 2BA T&R PRESSURE SEN



TE Part #823776-000  
382A012-3-0



TE Part #E74832-000  
B-155-9003



TE Part #F40876-000  
B-155-9002

Documents

Product Drawings  
AMP LEAF KEYING PLUG  
English

Product Specifications  
Product Specification  
English  
Connector, AMP-LEAF, .000030 Gold Plated Contacts, DPH Housing  
English



Product Specification

English

Connector, AMP-LEAF, Phenolic or Thermoplastic Housing

English

Product Specification

English

Connector, AMP-LEAF, Tin Plated Contact

English

Instruction Sheets

Instruction Sheet (U.S.)

English