



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Shield**

Strain Relief: **Without**

Primary Product Color: **Black**

Primary Product Material: **PBT**

Number of Positions: **8**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Shield
---	--------

Configuration Features

Number of Positions	8
---------------------	---

Body Features

Primary Product Color	Black
Primary Product Material	PBT

Mechanical Attachment

Strain Relief	Without
---------------	---------

Usage Conditions

Operating Temperature (Max)	130 °C[266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 965601-2
8POS MQS REC COD II

Customers Also Bought

TE Part #1-968879-1
MT2/JPT70P BUGH KPL

TE Part #1-2112891-1
36POS,TAB 1.5X0.6,TAB HSG,ASSY

TE Part #282079-2
AMP SUPERSEAL 1.5 SERIES 1P PL

TE Part #2-1418448-1
3 POS AMP MCP1.5k REC. HSG COD



TE Part #929939-1
[JPT REC 2.8 Contact SWS Sn](#)

TE Part #1241416-1
[AMP MCP 6.3/4.8K, CONTACT, SWS](#)

TE Part #284223-4
[24 POS.KIT ASSY FOR AIR BAG \(B](#)

TE Part #2600031-1
[4CCT BLACK PLUG W/SMALL SEAL](#)

TE Part #2822356-1
[070 TYPE NEW RUBBER PLUG S](#)

TE Part #8-2337030-2
[FLAP,ASSY COMBO 2, LEFT](#)

Documents

Product Drawings

[MQS KAPPE 8P](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-965600-1_B.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-965600-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-965600-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.