


[Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories >](#)

DEUTSCH DRB Mounting Accessories

Automotive Connector Accessory Type: **Mounting Frame**Primary Product Material: **PA GF**Primary Product Color: **Black**Number of Positions: **102, 128**Operating Temperature Range: **-55 – 125 °C [-67 – 257 °F]**[All DEUTSCH DRB Mounting Accessories \(6\)](#)

## Features

### Product Type Features

Automotive Connector Accessory Type

Mounting Frame

### Configuration Features

Number of Positions

102, 128

### Body Features

Primary Product Material

PA GF

Primary Product Color

Black

### Usage Conditions

Operating Temperature Range

-55 – 125 °C [-67 – 257 °F]

### Industry Standards

UL Flammability Rating

Not tested

### Packaging Features

Packaging Quantity

1

## Packaging Method

Box

**Other**

Serviceable

Yes

**Product Compliance**For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023  
(235)Candidate List Declared Against: JUNE  
2023 (235)SVHC > Threshold:  
Octamethylcyclotetrasiloxane (D4) (.5% in  
Component Part)  
Dodecamethylcyclohexasiloxane (D6) (.5%  
in Component Part)  
Decamethylcyclopentasiloxane (D5) (.5% in  
Component Part)**Article Safe Usage Statements:**  
Wash thoroughly after handling. Recycle if possible and dispose of the article by  
following all applicable governmental regulations relevant to your geographic  
location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900  
ppm.


Solder Process Capability

Not reviewed for solder process capability

## Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**




TE Part # CAT-D781-CH8172  
DEUTSCH DRB Housings


## Also in the Series | DEUTSCH DRB




Automotive Connector Caps & Covers (2)




Automotive Connector Locks & Position Assurance(20)



Automotive Housings(19)



Insertion & Extraction Tools(1)



Other Automotive Connector Accessories(6)

## Customers Also Bought



TE Part #WB-51SAL  
DEUTSCH DRB Wedgelocks



TE Part #2298173-1  
DT04-08PA-P089, REC, 8P GRY,  
BUSBAR,3X2,A



TE Part #1-2328352-2  
25POS, MIXED,REC HSG,ASSY,  
SEALED, COD A



TE Part #DRB12-128PAE-L018  
REC, 128P, BLK, E, CAP, A




TE Part #9-2367345-1  
SOC CONN CVR ASSY,2POS,CSS  
SIZE 20,180



TE Part #2500021-1  
SRC Pwr 60+6AG Male Blade Hsg Assy



TE Part #K5000061  
Batt. Disconnector 35-314-131-R-901



TE Part #1718027-2

## Documents

### Product Drawings

[FLANGE, MOUNT, 102/128P, BLK, A](#)

English

---

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_DRBF-1A\\_99.2d\\_dxf.zip](#)

English

### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_DRBF-1A\\_99.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_DRBF-1A\\_99.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[CONNECTOR SELECTOR](#)

English

---

### Product Specifications

[Application Specification](#)

English