




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **22**
Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Dual Positions	22
Number of Positions	22
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Type	Socket
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
Panel Mount Feature Type	Mounting Ears
Connector Mounting Type	Board Mount

Housing Features

Housing Entry Configuration	Both Ends Closed
Housing Material	Diallyl Phthalate
Centerline (Pitch)	3.96 mm[.156 in]

Dimensions

Connector Length	108.74 mm[4.281 in]
Connector Height	8.89 mm[.35 in]
PCB Thickness (Recommended)	1.4 – 1.78 mm[.055 – .07 in]
Row-to-Row Spacing	4.14 mm[.163 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

Packaging Features

Packaging Quantity	250
Packaging Method	Box

Other

Discrete Wire Connector Comment	Housing per MIL-M-14F.
---------------------------------	------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)
Candidate List Declared Against: JUNE 2023 (235)
SVHC > Threshold:
tris(2-methoxyethoxy)vinylsilane (.11% in Component Part)
Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 465195-1
AMP-LEAF EXTRACTION TOOL

Customers Also Bought



TE Part #4108170001
HT-SCE-1/8-2.0-9



TE Part #YD369-HR66-NS00000
369 HARSH 6 WAY REC, SKT - BACC65CR2SN



TE Part #1623927-2
CFR16 5% 100R



TE Part #CS9490-000
SEB-A





TE Part #ZPF000000000008538
983-6S 10-05 S6



TE Part #ZPF000000000008542
983-6S 10-05 S7



TE Part #ZPF000000000008545
983-6S 10-05 S8



TE Part #ZPF000000000008547
983-6S 10-05 S9



TE Part #ZPF000000000008680
983-6S 22-19 PN-L

TE Part #1752750001
TMS-SCE-1/4-2.0-2

Documents

Product Drawings

HSG AMP LEAF 22 POS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_480142-2_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_480142-2_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_480142-2_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Connector, AMP-LEAF, .000030 Gold Plated Contacts, DPH Housing

English

Product Specification

English

Connector, AMP-LEAF, Phenolic or Thermoplastic Housing

English



Product Specification

English

Connector, AMP-LEAF, Tin Plated Contact

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Instruction Sheets

Instruction Sheet (U.S.)

English

INTER-CONTACT KEYING PLUG NO. 583274-1 FOR AMP-LEAF CONNECTORS

English

Agency Approvals

Agency Approval Document

English