

DTS26F09-98SN [V001]

✓ ACTIVE

DEUTSCH | DEUTSCH 38999, DEUTSCH 38999 Series III

TE Internal #: YDTS26F09-98SNV001

Standard Circular Connectors, Cable-to-Panel, 3 Position, Sealable,
Wire & Cable, Signal, Panel Mount, Electroless Nickel, DEUTSCH
38999 Series III

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors > Straight Plug: D38999, 09-98 Insert, Electroless Nickel Plating



Connector System: **Cable-to-Panel**
Number of Positions: **3**
Sealable: **Yes**
Connector & Contact Terminates To: **Wire & Cable**
Contact Current Rating (Max): **7.5 A**

[All Straight Plug: D38999, 09-98 Insert, Electroless Nickel Plating \(71\)](#)

Features

Product Type Features

Product Type	Connector Assembly
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Straight Plug

Configuration Features

Number of Positions	3
Number of Power Positions	0
Number of Signal Positions	3
Contacts Preloaded	No

Body Features

Shell Plating Material	Electroless Nickel
Shell Base Material	Aluminum 6061-T6
Circular Connector Insulation Material Type	Hard Dielectric/Silicone
Hermetically Sealed	No



Contact Features

Contact Current Rating (Max)	7.5 A
Reverse Gender	No
Contact Layout Arrangement	9 – 98
Circular Connector Contact Type	Socket

Mechanical Attachment

Connector Mounting Type	Panel Mount
Polarization Code	N
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	9
Alignment Keyed	Clocking

Dimensions

Wire Size	.2 – .52 mm ²
-----------	--------------------------

Usage Conditions

Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
Shielded	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-D38999-DTS1B D38999: Square Flange, 9-98 insert	 TE Part # CAT-D38999-DTS9P Jam Nut: D38999, 09-98 Insert, Electroless Nickel Plating	 TE Part # YDTS20Y09-98PNV001 HERM RECP	 TE Part # DTS20Y09-98PN HERM RECP
 TE Part # YDTS20Y09-98XNV001 HERM RECP	 TE Part # DTS21Y09-98PN HERM RECP	 TE Part # YDTS24Y09-98PNV001 HERM RECP	 TE Part # YDTS21H09-98CNV001 HERM RECP
 TE Part # YDTS21H09-98PNV001 HERM RECP	 TE Part # YDTS21H09-98XNV001 HERM RECP	 TE Part # YDTS23H09-98CNV001 HERM RECP	 TE Part # YDTS23H09-98XNV001 HERM RECP



TE Part # YDTS20H09-98CN0000
HERM RECP

TE Part # YDTS20H09-98PN0000
HERM RECP

TE Part # YDTS20H09-98XN0000
HERM RECP

TE Part # YDTS20N09-98CNV001
HERM RECP

TE Part # YDTS20N09-98PNV001
HERM RECP

TE Part # YDTS20N09-98XNV001
HERM RECP

TE Part # YDTS20Y09-98CNV001
HERM RECP

TE Part # YDTS20Y09-98XN0000
HERM RECP

Also in the Series | **DEUTSCH 38999**

Standard Circular Connectors(12476)

Also in the Series | **DEUTSCH 38999 Series III**

Standard Circular Connectors(37353)

Customers Also Bought





TE Part #510715-000
Low Profile Heat Shrink Boots: Poly Molded, Lipped, Straight



TE Part #4-640443-0
10P MTA100 CONN ASSY GRN



TE Part #YDTS20F13-35SNV001
RECP ASSY



TE Part #YDTS26F09-98PNV001
PLUG ASSY



TE Part #YDTS20F09-98PNV001
RECP ASSY



TE Part #YDTS26F11-02SNV001
PLUG ASSY



TE Part #YDTS26F11-05PNV001
PLUG ASSY



TE Part #EB1UM-00001V-300PA
PRESS XDCR EB1UM-00001V-300PA

TE Part #M3021-000005-2K5PG
PRESS XDCR M3021-000005-2K5PG

Documents

Product Drawings

PLUG ASSY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_YDTS26F09-98SNV001_99.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_YDTS26F09-98SNV001_99.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_YDTS26F09-98SNV001_99.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



DEUTSCH DTS Series Connectors for 38999 QRG

English