

1437719-8  ACTIVE

TE Internal #: 1437719-8

Circular Connector Caps & Covers, Sealable

[View on TE.com >](#)

Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Caps & Covers



Sealable: Yes

Features

Product Type Features

Sealable	Yes
----------	-----

Packaging Features

Packaging Quantity	250
Packaging Method	Carton

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (3.5% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1437719-5
T01-0500-P=INDUSTRIAL CONNECTO

Customers Also Bought



TE Part #2-6609115-3
6EGG1-2=F7386D



TE Part #281739-3
HEADER HE14 STRAIGHT 2X3 P



TE Part #3-2176055-2
RLP73K 2B R20 1% 1K RL



TE Part #2-1437719-1
T01-0550-P05-MALE PLUG
CONNECTOR SOLDER



TE Part #1676300-2
RN 0805 30K1 0.1% 10PPM 1KRL



TE Part #1-1879417-0
CPF 0603 430K 0.1% 25PPM 1K RL




TE Part #1-1614883-3
CPF0805 470R 0.1% 25PPM 1K RL



TE Part #8-1879377-6
CRGH0805 5% 3K3 0.33W



TE Part #8503232002
DWTC-12/3-X-STK



TE Part #5070054026
RNF-100-3/16-X-SP

Documents

Product Drawings

T01-0500-S=INDUSTRIAL CONNECTO

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_1437719-8_A1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_1437719-8_A1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1437719-8_A1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1437719-8_A1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1437719-8_A1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1437719-8_A1.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English