



Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories



Automotive Connector Accessory Type: **Mounting Frame**

Primary Product Material: **PA GF**

Primary Product Color: **Black**

Number of Positions: **1**

Operating Temperature Range: **-55 – 125 °C [-67 – 257 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Mounting Frame
-------------------------------------	----------------

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Material	PA GF
Primary Product Color	Black

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	Not tested
------------------------	------------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Serviceable	Yes
-------------	-----



Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # DTSK04-1-08PA
RECEPTACLE, INLINE, KEY A

TE Part # DTSK04-1-08PB
RECEPTACLE, INLINE, KEY B

TE Part # DTSK04-1-08PC
RECEPTACLE, INLINE, KEY C

Also in the Series | DEUTSCH DT

Automotive Connector Caps & Covers
(47)

Automotive Connector Locks &
Position Assurance(74)

Automotive Housings(620)

Connector Backshells(58)

Connector Seals & Cavity Plugs(6)

Insertion & Extraction Tools(3)

Other Automotive Connector
Accessories(27)

PCB Headers & Receptacles(103)


Also in the Series | DEUTSCH DTHD

Automotive Housings(22)


Other Automotive Connector
Accessories(1)

Customers Also Bought





TE Part #1775470-8
HPI CONN., 2.0MM, V/T, SMT, 8P, 80U"



TE Part #36272
TERMINAL,SOLIS FLAG R 12-10



TE Part #K1011766
Relay 29-214-11



TE Part #16-04477
GASKET, 24SZ, BLK, HD30



TE Part #DTSK04-1-08PB
RECEPTACLE, INLINE, KEY B



TE Part #DTSK06-1-08SA
PLUG, INLINE, KEY A



TE Part #DTSK06-1-08SB
PLUG, INLINE, KEY B



TE Part #SRK-PC-080-32-601
PIN, SOLID, SIZE M8, 32mm2, AG



TE Part #SRK-SC-080-25-601
SOC, SOLID, SIZE M8, 25mm2, AG



TE Part #SRK-SC-080-35-601
SOC, SOLID, SIZE M8, 35mm2, AG

Documents

Product Drawings

DTSKF-1, DTSK FLANGE MOUNT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2289235-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2289235-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2289235-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[DEUTSCH DTSK Connectors Series Brief](#)

English

[ICT Terminals and Connectors Catalogue](#)

English

[DEUTSCH DTSK Components Infographic](#)

English

[Product Specifications](#)

[Application Specification](#)

English