

Connectors > Connector Accessories > Connector Backshells > Connector Backshell Accessories: Clamp Shell, Tool-less Assembly



Connector Backshell Product Type: **Backshell Kit**

Number of Positions: **8**

Sealable: **No**

Compatible With Connector Shape: **Rectangular**

Operating Temperature Range: **-65 – 175 °C [-85 – 347 °F]**

[All Connector Backshell Accessories: Clamp Shell, Tool-less Assembly \(7\)](#)

Features

Product Type Features

Connector Backshell Product Type	Backshell Kit
Sealable	No

Configuration Features

Number of Positions	8
---------------------	---

Housing Features

Compatible With Connector Shape	Rectangular
---------------------------------	-------------

Usage Conditions

Operating Temperature Range	-65 – 175 °C [-85 – 347 °F]
-----------------------------	-----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Out of Scope
-----------------------------	--------------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # ZPF000000000099713
DMC-MD 20 N

Customers Also Bought



TE Part # ZPF000000000099713
DMC-MD 20 N



TE Part # YD369-P66-NS300000
369 6 WAY PLUG, 20/22 CONTACTS,
SKT



TE Part # YDTS20F09-35ANV001
RECP ASSY



TE Part # ZPF000000000099707
DMC-M 99-01 AN

TE Part #ZPF000000000107346 787-0011-00	TE Part #ZPF000000000106824 787-8017-00	TE Part #EK2882-000 222K163-3-CS-2068-0	TE Part #Y72513-23-55PNV004 HERM RECP
<hr/>			
TE Part #CP0058-000 RMK-8X30-A4-CS34034			

Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_ZPF000000000105765_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_ZPF000000000105765_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_ZPF000000000105765_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DMC-M Series Single Module EN4165](#)

English