

**104693-6**

✓ ACTIVE

**AMPMODU | AMPMODU 50/50 Grid**

TE Internal #: 104693-6


PCB Mount Header, Vertical, Board-to-Board, 60 Position, 1.27 mm

[.05 in] Centerline, Fully Shrouded, Gold, Surface Mount, Black,

AMPMODU 50/50 Grid

[View on TE.com >](#)

Connectors &gt; PCB Connectors &gt; PCB Headers &amp; Receptacles

PCB Connector Assembly Type: **PCB Mount Header**PCB Mount Orientation: **Vertical**Connector System: **Board-to-Board**Number of Positions: **60**Number of Rows: **2**

## Features

### Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	60
Number of Rows	2
Board-to-Board Configuration	Parallel

### Electrical Characteristics

Dielectric Withstanding Voltage (Max)	300 VAC
Operating Voltage	30 VAC

### Body Features

PCB Retention Feature Material	Copper Alloy
PCB Retention Feature Plating Material	Tin-Lead over Nickel
Connector Profile	Standard

Primary Product Color	Black
-----------------------	-------

#### Contact Features

	150 $\mu$ in
Mating Pin Diameter	.46 mm [.018 in]
Contact Shape & Form	Round
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Gold
Contact Type	Pin
Contact Current Rating (Max)	.5 A

#### Termination Features

Round Termination Post & Tail Diameter	.46 mm [.018 in]
Termination Method to Printed Circuit Board	Surface Mount

#### Mechanical Attachment

PCB Mount Retention Type	Hold-Down Post
Mating Alignment	With
Mating Alignment Type	Keyed
PCB Mount Retention	With

#### Housing Features

Centerline (Pitch)	1.27 mm [.05 in]
Housing Material	Thermoplastic

#### Dimensions

Row-to-Row Spacing	1.27 mm [.05 in]
Stack Height	9.91 mm [.39 in]

#### Usage Conditions

Operating Temperature Range	-65 – 105 °C
-----------------------------	--------------

#### Industry Standards

Approved Standards	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0

#### Packaging Features

Packaging Quantity	13
--------------------	----

Packaging Type

Box, Tube

## Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU

Not Compliant

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023  
(235)

Candidate List Declared Against: JUNE  
2023 (235)

SVHC &gt; Threshold:

Pb (13% in Component Part)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per  
homogenous material. Also BFR/CFR/PVC  
Free


Solder Process Capability

Reflow solder capable to 260°C

### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




TE Part # 104652-6  
60 50/50 GRID DRST SFMNT RCPT

## Also in the Series | AMPMODU 50/50 Grid




Insertion &amp; Extraction Tools(1)



PCB Connector Covers(9)






PCB Headers &amp; Receptacles(302)



Ribbon Cable Connectors(34)

## Customers Also Bought

TE Part #1601070-2  
131-137-014-TAB,059X032,STDSTMZTE Part #Y5015-000000004245  
FIXED, REAR MOUNT SOCKET  
CONNECTORTE Part #103672-5  
06 MTE HDR SRRA LATCH W/HLDWNTE Part #1759898-1  
0.6 BTB 50 Posn MH\_5.5 PlugTE Part #1969605-2  
2P PM PLUG VAL-U-LOK PM GWTE Part #277148-3  
TERMINAL,COPALUM R 6 5/16TE Part #63754-1  
TERM,MAG-MATE 27-23 016TPBRTE Part #6600390-1  
MBXL VERT HDR 4P STRTE Part #Y5015-00000078029  
LOCKING BACK NUTTE Part #Y5015-00000077955  
GROMMET

## Documents

### Product Drawings

60 50/50 HDR DRST SFMNT .390

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_104693-6\\_K.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_104693-6\\_K.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_104693-6\\_K.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Product Specifications**

[Application Specification](#)

English

---

**Product Environmental Compliance**

[Product Compliance Document](#)

English

[Product Compliance Document](#)

English

---

**Agency Approvals**

[UL Report](#)

English