




EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > CORCOM GG SERIES MULTI-FUNCTION INLET FI



Filter Type: **Power Entry Module**

Input Voltage Selection: **None**

Filter Switch Type: **No Switch**

Filter Shield Type: **Shielded**

Product Orientation: **Right Angle**

[All CORCOM GG SERIES MULTI-FUNCTION INLET FI \(36\)](#)

Features

Product Type Features

|                         |                    |
|-------------------------|--------------------|
| Ground Choke Option     | No                 |
| Filter Type             | Power Entry Module |
| Filter Switch Type      | No Switch          |
| Output Termination Type | .250" FASTON       |
| Filtering Requirements  | Filtered           |
| Filter Connector Type   | IEC 320/C-14       |

Configuration Features

|              |      |
|--------------|------|
| Fuse Options | Dual |
|--------------|------|

Electrical Characteristics

|                                      |             |
|--------------------------------------|-------------|
| Input Voltage Selection              | None        |
| Leakage Current (Max) (120VAC, 60Hz) | 250 $\mu$ A |
| Leakage Current (Max) (250VAC, 50Hz) | 420 $\mu$ A |



|                   |         |
|-------------------|---------|
| Current Rating    | 1 A     |
| Operating Voltage | 250 VAC |

Body Features

|                     |             |
|---------------------|-------------|
| Filter Shield Type  | Shielded    |
| Product Orientation | Right Angle |

Mechanical Attachment

|                          |         |
|--------------------------|---------|
| Panel Mount Feature Type | Flanged |
|--------------------------|---------|

Usage Conditions

|                             |             |
|-----------------------------|-------------|
| Operating Temperature Range | -10 – 40 °C |
|-----------------------------|-------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                  |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-G34  
CORCOM GG SERIES MULTI-FUNCTION INLET FI

TE Part # 1609116-6  
10EHGS1-2=F8242

Also in the Series | Corcom GG

Multi-Function Inlet Filters(36)

Customers Also Bought

TE Part #6609059-2  
3EZ1=F7328 S0

TE Part #3-1393788-6  
V23079B1203B301

TE Part #5-292177-1  
MINI DRAWER CONN FOR CT 14P

TE Part #826467-3  
3P MOD II SHROUDED HEADER, ST

TE Part #5-1609152-1  
20SRB1=F8424

TE Part #T4161110004-003  
RPC-M12-MS-4CON-PVC-1.5SH

TE Part #5-826662-0  
50P AMPMODU II STIFT LEI

TE Part #254537-E  
SMCQ 20 M AB VV 8-03 CL \* H007 137 E005

TE Part #2176387-6  
RQ 1206 150K 0.1% 10PPM 1K RL

TE Part #1462041-6  
IMB06CTS=IM RELAY 140mW12V HDV



Documents

Product Drawings

1EGG1-2 (NEW GEN=F7642D S0

English

CAD Files

Customer View Model

ENG\_CVM\_6609115-3\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_6609115-3\_B.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_6609115-3\_B.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_6609115-3\_D.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_6609115-3\_D.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_CVM\_6609115-3\_D.2d\_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001\_CORCOM\_PRODUCT\_GUIDE

English

1654001\_CORCOM\_PRODUCT\_GUIDE\_GG\_HG

English

Corcom Combined Selector Charts

English

1-1654250-1\_CORCOM\_EMI\_RFI\_QRG

English

Product Environmental Compliance

TE Material Declaration

English