



VAL-U-LOK

TE Internal #: 1969605-4
Rectangular Power Connectors, Housing, Plug, Wire-to-Panel /
Wire-to-Wire, 4 Position, 4.2 mm [.165 in] Centerline, Wire & Cable,
UL 94V-2

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**
Connector & Housing Type: **Plug**
Connector System: **Wire-to-Panel, Wire-to-Wire**
Number of Positions: **4**
Centerline (Pitch): **4.2 mm [.165 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	2

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Retention Within Housing	Without
Contact Type	Pin



Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	4.2 mm[.165 in]
Housing Color	White
Housing Material	Polyamide

Dimensions

Connector Height	11.6 mm[.457 in]
Product Width	23.9 mm[.94 in]
Product Length	9.6 mm[.378 in]
Row-to-Row Spacing	4.2 mm[.165 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

CSA Rating	208567
UL Rating	Recognized
Agency/Standard	CSA, UL
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-2
Glow Wire Rating	GWT 750°C (Without Flame)

Packaging Features

Packaging Quantity	500
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1586039-4
4P VAL-U-LOK VRT HDR W/P V2



TE Part # 1969603-4
4P RCPT VAL-U-LOK GW

Customers Also Bought



TE Part #281839-5
HOUSING HE13 HE14 COSI 2X5 P



TE Part #188744-1
CONTACT REC HE14 COSI TIN PLATED



TE Part #T4071017041-001
M8.FMLE.PNLREAR.4POS.STR WIRE




TE Part #5205817-3
FEMALE SCREWLOCK KIT







TE Part #280095-2
FF 250 REC 0.3-0.8MM2 PTBR



TE Part #794955-1
VAL-U-LOK PIN BR SN 22-18AWG



TE Part #794956-1
VAL-U-LOK SKT BR SN 22-18AWG



TE Part #1969603-4
4P RCPT VAL-U-LOK GW



TE Part #2120958-1
M8 MALE SOCKET WITH WIRES, 0.25 SQMM



TE Part #T3609200122-000
DLX-20-MB

Documents

Product Drawings

4P PM PLUG VAL-U-LOK PM GW

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1969605-4_A_c-1969605-4-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1969605-4_A_c-1969605-4-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1969605-4_A_c-1969605-4-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773730-3 VAL-U-LOK Connectors with TPA Flyer

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

1969605-4

Rectangular Power Connectors, Housing, Plug, Wire-to-Panel / Wire-to-Wire, 4
Position, 4.2 mm [.165 in] Centerline, Wire & Cable, UL 94V-2



English

Instruction Sheets

Instruction Sheet (U.S.)

English