




Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Covers



Connector Cover Type: **Terminating**
Number of Positions: **50**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Connector Cover Type	Terminating
----------------------	-------------

Configuration Features

Number of Positions	50
---------------------	----

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)
Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58430-1
TOOL, REPAIR

Also in the Series | AMPLIMITE 0.50 Series

Connector Backshells(31)

D-Sub Covers(20)

D-Sub Locking & Mounting(8)

IDC D-Sub Connectors(66)



Insertion & Extraction Tools(1)



PCB D-Sub Connectors(172)

Customers Also Bought



TE Part #5749621-7
68 50S CABLE PLUG CONN/COV KIT



TE Part #1658659-1
KIT,HDP-20,ENCLSUR,PLUG,SIZE 3



TE Part #552285-1
ASSY, PLUG, 64 POS, B SLOT




TE Part #552008-1
KIT, COVER, 180, 50 POS



TE Part #5229911-1
SCREW,PAN HD,"CHAMP
PACKAGING



TE Part #5406436-1
MJ,TE,8P,SHLD W/PNL STPS



TE Part #5206052-3
SCREW,SPECIAL,ZN



TE Part #EC7554-000
HL104WE1TS038B



TE Part #206500-1
PLUG ASSY,26 POSN,Sz2,AMPLIMITE



TE Part #6828130-1
CO KIT, LC, SM, DUP TIGHT

Documents

Product Drawings

50 50SR TERMINATOR COVER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-750877-5_P.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-750877-5_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-750877-5_P.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Customer Manual \(U.S.\)](#)

English