



EMI & EMC Solutions > EMI Filters > IEC Unfiltered Inlets > IEC Unfiltered Inlets, Corcom C Series



Current Rating: 15 A

Filter Connector Type: IEC 60320-1 C-14

Filter Connector Style: Male Receptacle

Output Termination Type: 3/16" Faston

[All IEC Unfiltered Inlets, Corcom C Series \(8\)](#)

Features

Product Type Features

Filter Connector Type	IEC 60320-1 C-14
Filter Connector Style	Male Receptacle
Output Termination Type	3/16" Faston

Electrical Characteristics

Operating Voltage	250 VAC
Current Rating	15 A

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)



Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-102
CORCOM C SERIES MULTI-FUNCTION INLET FIL




TE Part # 1-1609112-4
15CBE1=F8274

Also in the Series | Corcom C



IEC Unfiltered Inlets(8)



Multi-Function Inlet Filters(8)

Customers Also Bought






TE Part #6609107-2
CORCOM P SERIES MULTI-FUNCTION INLET FIL



TE Part #9-2176231-8
SMD Power Resistor: 3 Watt, 1% Tol




TE Part #6609109-1
PE000DL6C M0=C7001



TE Part #350968-2
MR PIN 26-24 AU/PHBZ



TE Part #34159
TERMINAL,PG R 16-14 6



TE Part #5-103171-1
MOD IV RECP PLTD 15 DPLX LF



TE Part #4-1393144-2
K10P-11A15-240=K10/K20



TE Part #5748078-1
SLIDELATCH KIT

Documents

Product Drawings

15CBS1=F8273

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1609112-3_C_c-1-1609112-3-c.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1609112-3_C_c-1-1609112-3-c.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1609112-3_C_c-1-1609112-3-c.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_CORCOM_PRODUCT_GUIDE

English

1654001_Corcom_Product_Guide_C_Series

English

Corcom Combined Selector Charts

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English



CORCOM_C_SERIES_15AMP_POWER_ENTRY_MODULE

English

Agency Approvals

C Series Appliance Inlet CB Certificate

English

C Series Appliance Inlet CB Test Report

English