

PMOS0SS60

✓ ACTIVE


TE Internal #: 1-6609941-2

Multi-Function Inlet Filters, Power Entry (Filtered/Unfiltered), Single AC Input, DPST, None, Vertical, 6A Current Rating, .187" FASTON Output

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters



Filter Type: **Power Entry (Filtered/Unfiltered)**

Input Voltage Selection: **Single AC**

Filter Switch Type: **DPST**

Filter Shield Type: **None**

Product Orientation: **Vertical**

Features

Product Type Features

Ground Choke Option	No
Level Of Filtering	Inductor & Capacitor
Filter Type	Power Entry (Filtered/Unfiltered)
Filter Switch Type	DPST
Output Termination Type	.187" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-14

Configuration Features

Extender Options	None
Fuse Options	Single

Electrical Characteristics

Input Voltage Selection	Single AC
Leakage Current (Max) (120VAC, 60Hz)	2 μ A
Leakage Current (Max) (250VAC, 50Hz)	5 μ A



Current Rating	6 A
Operating Voltage	115 VAC, 230 VAC

Body Features

Filter Shield Type	None
Product Orientation	Vertical

Mechanical Attachment

Panel Mount Feature Type	Flanged
--------------------------	---------

Dimensions

Panel Thickness (Recommended)	.79 – 2 mm[.031 – .079 in]
-------------------------------	----------------------------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 7-6609941-0
PM00XDH6B=C3484

TE Part # 7-6609941-8
PM00XDS3B=C3492

Customers Also Bought

TE Part #34541
PIDG SPD 22-16 COMM 22-18MIL 6

TE Part #5226978-3
RTANG JK W/FLANGES, BNC PCB

TE Part #749805-9
KIT,HDP-20,PLUG,SIZE 3, 25 POS

TE Part #749806-7
KIT,HDP-20,RCPT,SIZE 1, 9 POSN

TE Part #641832-1
06P UMNL PIN HDR ASSY V2 NATL

TE Part #35772
TERMINAL,SOLIS R 12-10 1/4

TE Part #350429-1
03P UMNL PIN HDR ASSY NATL

TE Part #1-1825138-5
A201P3ZQ04

TE Part #5406206-2
MJ ASSY,6P,8POS,SHLD,CAT5e,NS

TE Part #003421-000
55A1822-18-9/96-9CS2275

Documents

Product Drawings
PM0S0SS60=C3426

English

CAD Files
Customer View Model
ENG_CVM_1-6609941-2_A.3d_igs.zip

English



Customer View Model

[ENG_CVM_1-6609941-2_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-6609941-2_A.2d_dxf.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_CVM_1-6609941-2_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-6609941-2_O.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-6609941-2_O.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English