




AMP-LATCH

TE Internal #: 2-1658526-0
Ribbon Cable Connectors, Wire-to-Board, 40 Position, 2.54 mm [.1 in] Centerline, 2 Row, Receptacle, Polarization Mating Alignment Type, Wire & Cable
[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Connector System: **Wire-to-Board**
Number of Positions: **40**
Centerline (Pitch): **2.54 mm [.1 in]**
Row-to-Row Spacing: **2.54 mm [.1 in]**
Number of Rows: **2**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	40
Number of Rows	2

Body Features

Primary Product Color	Blue
-----------------------	------

Contact Features

Wire Contact Termination Area Plating Thickness	2.54 – 5.08 μm[100 – 200 μin]
Wire Contact Termination Area Plating Material	Tin
	30 μin
Contact Mating Area Plating Material	Gold



Contact Current Rating (Max)	1 A
------------------------------	-----

Termination Features

Rectangular Termination Post & Tail Thickness	.36 mm[.014 in]
Rectangular Termination Post & Tail Width	.46 mm[.018 in]
Termination Method to Wire & Cable	Insulation Displacement (IDC)

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as




EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-AM74-UN384H AMP-LATCH UNIVERSAL HEADERS	 TE Part # 1-5088450-0 PULL LOOP, CUT LENGTH 2.32 IN	 TE Part # 1-1761607-3 IDC LOW PRO HDR 40P RA LG LAT BLK	 TE Part # 5104338-8 A/L LOW PRO HDR 40P VERT HT
 TE Part # 1-1761608-3 IDC LOW PRO HDR 40P VERT SHT L	 TE Part # 1-1761609-3 IDC LOW PRO HDR 40P RA SHT LAT	 TE Part # 5103308-8 A/L LOW PRO HDR 40P VERT BLACK	 TE Part # 5103310-8 A/L LOW PRO HDR 40P RA BLACK
 TE Part # 3-1761606-3 IDC LOW PRO HDR 40P VERT LG LA	 TE Part # 1-1761606-3 IDC LOW PRO HDR 40P VERT LG LAT BLK	 TE Part # 5103309-8 A/L LOW PRO HDR 40P VERT BLACK	 TE Part # 2-111506-4 040 UNIV I/O 30DP SLOT LTCH
 TE Part # 5103311-8 A/L LOW PRO HDR 40P RA BLACK	 TE Part # 1-1761681-3 IDC LOW PRO HDR 40P VERT HT BLACK	 TE Part # 2-111446-3 040 UNIV I/O 30DP NO EARS	 TE Part # 3-1761603-3 IDC LOW PRO HDR 40P VERT BLUE






TE Part # 3-1761605-3
IDC LOW PRO HDR 40P RA BLUE



TE Part # 3-1761607-3
IDC LOW PRO HDR 40P RA LG LAT



TE Part # 3-1761713-3
IDC LOW PRO HDR 40P VERT SHT L



TE Part # 5104340-8
A/L LOW PRO HDR 40P RA HT


Customers Also Bought



TE Part #1625959-3
HB03RE 100M 1% 100PPM




TE Part #2-1761603-6
IDC LOW PRO HDR 16P VERT BLUE



TE Part #2-1658526-9
609-1630LF=FSKT IDC S 16 30AU



TE Part #5749267-1
Mini DIN, 8 pos, R/A, Shield



TE Part #1-1734580-1
MOD-JacK,RJ45, 10P10C, SHD LP, 6u" Au



TE Part #3-1761603-3
IDC LOW PRO HDR 40P VERT BLUE



TE Part #502596-000
222K132-100-0

Documents

Product Drawings
609-4030LF FEM SOCKT,LEAD FREE

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2-1658526-0_C.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_2-1658526-0_C.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_2-1658526-0_C.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

Ribbon Cable Interconnect Solutions

English

Product Environmental Compliance

TE Material Declaration

English

Instruction Sheets

Instruction Sheet (U.S.)

English