



Connectors > RF Connectors > RF Connector Accessories > RF Connector Ferrules



Compatible With RF Cable Type: **RG 58, RG 58A, RG 58B, RG 58C**

Ferrule Inside Diameter: **5.3 mm, 5.31 mm [.209 in]**

Ferrule Material: **Copper**

Ferrule Plating Material: **Silver**

Compatible Insulation Diameter Range: **5.31 mm [.209 in]**

Features

Product Type Features

Compatible With RF Cable Type	RG 58, RG 58A, RG 58B, RG 58C
-------------------------------	-------------------------------

Body Features

Body Plating Material	Silver
-----------------------	--------

Contact Features

Ferrule Material	Copper
Ferrule Plating Material	Silver

Dimensions

Ferrule Inside Diameter	5.3 mm, 5.31 mm[.209 in]
Compatible Insulation Diameter Range	5.31 mm[.209 in]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)
Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #282105-1
AMP SUPERSEAL 1.5 SERIES 3P CA

TE Part #880811-2
COVER CAP, 3 WAY

TE Part #926894-3
UNIV.M-N-L.PIN


TE Part #164532-4
15P.HDP20 REC.ASSY.

TE Part #C56426-000
LKZ12B3

TE Part #183024-1
MINI MIC TAB L.P.

TE Part #5745007-1
RS449 LATCH BLOCK KIT

TE Part #282094-009
44A0211-20-9



Documents

Product Drawings

FERRULE-STRAIGHT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-328663-0_AA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-328663-0_AA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-328663-0_AA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

Agency Approval Document

English