




Connectors > PCB Connectors > Card Edge Connectors > Standard Edge Connectors



Connector System: **Wire-to-Board**
Number of Positions: **3**
Centerline (Pitch): **2.5 mm [.098 in]**
Termination Method to Wire & Cable: **Insulation Displacement (IDC)**
Number of Rows: **1**

Features

Product Type Features

Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Card Entry Style	Side
Number of Insulation Displacement Slots	3
Compatible With Wire & Cable Type	Discrete Wire
Number of Positions	3
Number of Rows	1
Connector Contact Load Condition	Selectively Loaded
PCB Mount Orientation	Right Angle

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features



Contact Retention Within Housing	With
Contact Type	Socket
Contact Mating Area Plating Material Thickness	3 – 6 µm
Contact Mating Area Plating Material	Tin
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Tin Alloy
Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention	Without
Mating Alignment	With
PCB Mount Alignment	Without
PCB Mount Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Entry Configuration	Both Ends Open
Centerline (Pitch)	2.5 mm[.098 in]
Housing Material	PA 6 GF

Dimensions

Connector Height	7.3 mm[.287 in]
PCB Thickness (Recommended)	1.5 mm[.059 in]
Compatible Insulation Diameter Range	1.2 – 1.6 mm[.047 – .063 in]
Wire Size	.22 – .35 mm²

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------



Packaging Features

Packaging Quantity	15400
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-1534797-2
AMP DUOPLUG MK2 CONNECTOR
12P



TE Part # 4-1534797-2
DUOPLUG MARK II CONNECTOR



TE Part # 3-1534797-1
AMP DUOPLUG MK2 CONNECTOR
11P



TE Part # 1-1740501-3
AMP DUOPLUG2.5 MK II HOUSING
W. PCB LOCK



TE Part # 3-1534796-3
AMP DUOPLUG MK2 CONNECTOR 3P

TE Part # 3-1534798-3
AMP DUOPLUG MK2 CONNECTOR 3P SELECTIVE

TE Part # 1740501-3
AMP DUOPLUG2.5 MKII CONN. 3P W. PCB LOCK

TE Part # 2-1534796-3
AMP DUOPLUG MK2 CONNECTOR 3P

TE Part # 3-1534797-3
AMP DUOPLUG MK2 CONNECTOR 13P

TE Part # 9-1740154-6
DUOPLUG MKII FEMALE HSG WITH PCB LOCKING

Customers Also Bought

TE Part #737015-3
PL TERMINAL RECEPTACLE 4-6 MM2 PTPBR

TE Part #3-1534796-5
AMP DUOPLUG MK2 CONNECTOR 5P

TE Part #3-1534797-1
AMP DUOPLUG MK2 CONNECTOR 11P

TE Part #1534415-4
DUOPL POW FEM CON4P

TE Part #1376477-4
2.5MM PITCH SIGNAL MATE CONN

TE Part #3-1534796-7
AMP DUOPLUG MK2 CONNECTOR 7P

TE Part #3-1534796-4
AMP DUOPLUG MK2 CONNECTOR 4P S

TE Part #3-1534796-3
AMP DUOPLUG MK2 CONNECTOR 3P

TE Part #2-1740918-3
AMP DUOPLUG2.5 MK II HOUSING W. PCB LOCK

TE Part #3-1534798-7
AMP DUOPLUG MK2 CONNECTOR 7P SELECTIVE

Documents



Product Drawings

DUOPLUG MKII FEMALE HSG WITH PCB LOCKING

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-1740154-3_D_c-9-1740154-3-d.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-1740154-3_D_c-9-1740154-3-d.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-1740154-3_D_c-9-1740154-3-d.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance Document

English

Product Compliance Document

English

Agency Approvals

VDE Certificate

English

VDE Certificate

English