

15EJH8

✓ ACTIVE


TE Internal #: 3-6609008-2

Multi-Function Inlet Filters, Power Line, Right Angle, 15A Current Rating, Wire Lead Output, Operating Voltage 250 VAC, Filtered, IEC 320/C-14

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters



Filter Type: **Power Line**

Product Orientation: **Right Angle**

Leakage Current (Max) (120VAC, 60Hz): **2 μ A**

Leakage Current (Max) (250VAC, 50Hz): **5 μ A**

Current Rating: **15 A**

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Output Termination Type	Wire Lead
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	2 μ A
Leakage Current (Max) (250VAC, 50Hz)	5 μ A
Current Rating	15 A
Operating Voltage	250 VAC

Body Features

Product Orientation	Right Angle
---------------------	-------------

Mechanical Attachment

Panel Mount Feature Type	Flanged
--------------------------	---------



Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #1-2273003-1
M8 x 1.0 straight socket Pigtail



TE Part #1-6609130-3
5EHM1S=F8115



TE Part #1-6609987-8
15SRB8=F8220H




TE Part #608036-1
SILICONE FUSION TAPE,1\"/>



TE Part #2110819-1
QSFP+ Enh EVERCLEAR PT Conn



TE Part #32945
PG R 22-16 COMM 22-18 MIL 6



TE Part #1-2273002-1
M8 x 1.0 straight plug Pigtail



TE Part #1-480305-0
03P CMNL CAP HSG F/H NATL



TE Part #ANT-5GW-FPC-V100M4
Antenna 5GW FPC LV 20x120 100 MHF4



TE Part #L9000343-01
Antenna GNSS FPC SH L1 25x25 100 MHF4

Documents

CAD Files

Customer View Model

[ENG_CVM_3-6609008-2_0.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_3-6609008-2_0.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_3-6609008-2_0.2d_dxf.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_CVM_3-6609008-2_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-6609008-2_O.3d_stp.zip](#)

English

15EJH8

Multi-Function Inlet Filters, Power Line, Right Angle, 15A Current Rating, Wire Lead Output, Operating Voltage 250 VAC, Filtered, IEC 320/C-14



Customer View Model

[ENG_CVM_CVM_3-6609008-2_O.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE_EEJ_SERIES](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English