




MTA 156

TE Internal #: 5-643819-0

Standard Rectangular Connectors, Connector Assembly,
Receptacle, Mating Alignment, Polarization Mating Alignment
Type, Mating Retention, MTA 156

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Mating Alignment: **With**
Mating Alignment Type: **Polarization**
Mating Retention: **With**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Cavities	20
Contacts Preloaded	Yes
Number of Positions	20
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features



Contact Type	Receptacle
Wire Contact Termination Area Plating Material	Tin
Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Tin
Contact Retention Within Housing	With
Contact Current Rating (Max)	7 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	Locking Ramp
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Housing Color	Red
Centerline (Pitch)	3.96 mm[.156 in]

Dimensions

Connector Height	18.42 mm[.725 in]
Product Width	9.02 mm[.355 in]
Product Length	79.25 mm[3.12 in]
Wire Size	.3 – .4 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	No
Circuit Application	Power

Industry Standards

CSA Rating	LR 7189
UL Rating	Recognized



Agency/Standard	CSA, UL
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	125
Packaging Method	Box & Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 58074-1
MTA 50/100/156 MANUAL TOOL
FRAME



TE Part # 59804-1
MAINTENANCE TOOL



TE Part # 2-644752-0
20P MTA156 HDR ASSY SQ STR F/L



TE Part # 2-640388-0
20P MTA156 HDR ASSY RN STR F/L



TE Part # 2-640389-0
20P MTA156 HDR ASSY SQ R/A F/L



TE Part # 58247-1
MTA 156 CRIMP HEAD REPAIR
DISCRETE



TE Part # 2-640445-0
20P MTA156 HDR ASSY FL/STR SN



TE Part # 2-640551-0
20P MTA156 COVER



TE Part # 2-640383-0
20P MTA156 HDR ASSY STR SQ SN



TE Part # 58247-3
MTA 156 CRIMP HEAD PRODUCTION
RBBN CABLE



TE Part # 2-640385-0
20P MTA156 HDR ASSY SQ R/A



TE Part # 2-640643-0
20P MTA156 COVER F/T




TE Part # 2-643067-0
20P MTA156 MOLDED COVER




TE Part # 2-643071-0
20P MTA156 FD-THRU COVER



TE Part # 2-644751-0
20P MTA156 HDR ASSY R/A



TE Part # 2-644753-0
20P MTA156 HDR ASSY RN STR F/L



TE Part # 58040-1
MTA 156 ARBOR FIXTURE DISCRETE
RBN CABLE



TE Part # 58247-2
MTA 156 CRIMP HEAD PRODUCTION
DISCRETE



TE Part # 58576-1
MTA 156 PNEUMATIC TOOL FOR
BOARD FIXTURE



TE Part # 58580-1
MTA 156 MANUAL TOOL ASSEMBLY
DISCRETE

Also in the Series | **MTA 156**



Insertion & Extraction Tools(1)




PCB Connector Covers(88)



PCB Connector Keying(2)



PCB Connector Mounting(1)




PCB Headers & Receptacles(314)



Power Contacts(2)



Rectangular Power Connectors(698)



Standard Rectangular Connectors(337)



Wire-to-Board Connector Contacts(2)


Customers Also Bought




TE Part #2-770849-0
20P SL156 HSG W/LCK RMP & TABS




TE Part #4-643819-8
18P MTA156 CONN ASSY 22AWG LF



TE Part #52749
SPLICE,COPALUM PARA 1/0



TE Part #1-640551-7
17P MTA156 COVER




TE Part #311906-000
FLTWC0311-22-7



TE Part #2-640385-0
20P MTA156 HDR ASSY SQ R/A



TE Part #91359-2
PRO-CRIMPER II DIE ASSEMBLY



TE Part #346427-000
FLTWC0311-22-4



Documents

Product Drawings

20P MTA156 CONN ASSY 22AWG LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-643819-0_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-643819-0_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-643819-0_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese

Agency Approvals

Agency Approval Document

English