




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Rectangular Tongue Terminal**

Wire Size: **10382 – 16507 CMA**

Stud Size: **#10**

Features

Product Type Features

Shape Description	Flat Sided
Stud Size	#10
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	2.029 g
----------------	---------

Contact Features

Contact Base Material	Brass
Spade Terminal Type	Rectangular Tongue Terminal
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin
Contact Underplating Material	None



Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	10382 – 16507 CMA
Stud Diameter	4.82 mm[.19 in]
Tongue Thickness	1.02 mm[.04 in]
Product Length	18.29 mm[.72 in]
Barrel Inside Diameter	3.3 mm[.13 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	110 °C[230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	5000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 42191-1
FLAG TERMINAL TERMINAL 18-12
AWG TPBR




TE Part # 2-2150860-1
OC-PA-E-FM-210F-001-0046




TE Part # 2-2150860-2
OC-PA-E-FA-210F-001-0292



TE Part # 2150860-1
OC-AT-E-FM-210F-001-0046




TE Part # 2150860-2
OC-AT-E-FA-210F-001-0292




TE Part # 7-2150860-7
OC-210F-CRIMPTOOLKIT
KIT
REPRESENTATION
ONLY


Customers Also Bought




TE Part #62057-1
250 FASTON FLAG REC 12-10 AWG
SPBZ



TE Part #60940-1
.058 PIN REC 24-20 010PTPPHBZ



TE Part #42868-2
SHUR PLUG 180 RECEPTACLE 14-10
AWG TPBR



TE Part #1742785-1
110 FASTON,REC.,22-18 AWG,PTBR






TE Part #62003-2
110 FASTON REC 22-18 AWG TPBR



TE Part #3-644726-6
06P MTA100 CONN ASSY W/TB LF



TE Part #520935-1
PLMKII&FASTON 250 REC HSG 2P NAT



TE Part #60376-1
PIN 090 RECEPTACLE 20-14 AWG TPPHBZ



TE Part #2151079-1
OCEAN_2.0_APPLICATOR-S-080F130F

Documents

Product Drawings

RING .190 (4.82 MM) 8-10 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42673-2_K_c-42673-2-k.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_42673-2_K_c-42673-2-k.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_42673-2_K_c-42673-2-k.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

42673-2

Rectangular Tongue Terminal, 10 – 8 AWG, #10 Stud Size, 4.82 mm [.19 in] Stud Diameter, Open Barrel, Straight, Tin, Uninsulated

