




MATE-N-LOK | Universal MATE-N-LOK

TE Internal #: 641968-3

Rectangular Power Connectors, Header, Receptacle, Wire-to-Board, 4 Position, 6.35 mm [.25 in] Centerline, Printed Circuit Board, Universal MATE-N-LOK

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **6.35 mm [.25 in]**

Features

Product Type Features

Rectangular Power Connector Type	Header
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	4
PCB Mount Orientation	Vertical
Number of Power Positions	4
Number of Signal Positions	0
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features



Multiple Contact Types	Without
Contact Layout	Inline
Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	12 A
Contact Retention Within Housing	Without
Contact Type	Pin
PCB Contact Termination Area Plating Material	Pre-Tin
Contact Mating Area Plating Material Thickness	3.81 – 5.08 µm[150 – 200 µin]

Termination Features

Termination Post & Tail Length	3.7 mm[.146 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Alignment Type	Standard Polarized Tail
Strain Relief	Without
Mating Alignment Type	Polarization
Mating Retention	With
Mating Alignment	With
PCB Mount Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Positive Lock
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	6.35 mm[.25 in]
Housing Color	Black
Housing Material	Nylon

Dimensions

PCB Thickness (Recommended)	3.12 mm[.124 in]
-----------------------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------



Industry Standards

CSA Rating	Certified, LR 7189
UL Rating	Recognized
Agency/Standard	CSA, UL, VDE
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 350793-1 04P UMNL PIN HDR ASSY 94VO	 TE Part # 350430-4 04P UMNL PIN HDR ASSY NATL LF	 TE Part # 350761-5 04P UMNL HDR ASSY PC LF	 TE Part # 350793-3 04P UMNL PIN HDR ASSY 94VO LF
 TE Part # 350430-1 04P UMNL PIN HDR ASSY NATL	 TE Part # 1-480703-9 04P UMNL CAP HSG BLK	 TE Part # 641969-1 06P UMNL PIN HDR ASSY V2 NATL	 TE Part # 350792-1 04P UMNL PIN HDR ASSY 94VO
 TE Part # 641968-1 04P UMNL PIN HDR ASSY POL 94VO	 TE Part # 641965-1 03P UMNL PIN HDR ASSY V2 NATL	 TE Part # 641964-1 02P UMNL PIN HDR ASSY POL 94VO	 TE Part # 641964-3 02P UMNL PIN HDR ASSY POL LF
 TE Part # 350780-1 04P UMNL CAP HSG	 TE Part # 641966-1 03P UMNL PIN HDR ASSY 94VO	 TE Part # 1-480703-0 04P UMNL CAP HSG NATL	 TE Part # 1586845-1 04P UMNL CAP HSG NATL, GW
 TE Part # 350761-4 04P UMNL HDR ASSY PC	 TE Part # 641967-1 04P UMNL PIN HDR ASSY POL NATL	 TE Part # 641974-1 12P UMNL PIN HDR ASSY 94VO	 TE Part # 643416-1 04P UMNL HDR ASSY POL 94VO

Also in the Series | Universal MATE-N-LOK



Circular Power Connectors(2)



Connector Contacts(2)



Connector Seals & Cavity Plugs(27)




Connector Strain Relief(34)



Insertion & Extraction Tools(4)



Power Contacts(207)



Rectangular Connector Adapters(7)



Rectangular Connector Hardware(1)



Rectangular Connector Housings(1)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(8)



Rectangular Power Connectors(672)

Customers Also Bought



TE Part #4-641215-0
10P MTA100 HDR ASSY FL/ST 30AU



TE Part #1-480438-0
16P CMNL PLUG HSG M/M NATL



TE Part #1-350944-0
04P UMNL HDR ASSY R/A 94VO



TE Part #1-794070-1
20P MINI UMNL HDR W/DH AU LF



TE Part #643406-1
05P UMNL PIN HDR ASSY POL 94VO



TE Part #1-770166-1
02P MINI UMNL ASSY VO SNAU LF



TE Part #640383-2
02P MTA156 HDR ASSY STR SQ SN



TE Part #643416-1
04P UMNL HDR ASSY POL 94VO



Documents

Product Drawings

04P UMNL PIN HDR ASSY POL 94VO

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_641968-3_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_641968-3_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_641968-3_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Instruction Sheets

Instruction Sheet (U.S.)

English