




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Contacts



Contact Type: **Socket**

Connector System: **Wire-to-Board**

Contact Mating Area Plating Material: **Tin-Lead**

Connector & Contact Terminates To: **Wire & Cable**

Circuit Application: **Power & Signal**

Features

Product Type Features

Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Contact Features

Contact Type	Socket
Contact Mating Area Plating Material	Tin-Lead

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)




Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 530509-8 DUO-TYNE FLG HSG 18 POS	 TE Part # 530501-5 CONT.DUO TYNE FLAG STRIP	 TE Part # 1-530509-8 18 DUO TYNE FLAG HSG	 TE Part # 2-4151009-1 OCEAN-2.0-APPLICATOR-S-090F1400
 TE Part # 2-4151009-2 OCEAN-2.0-APPLICATOR-S-090F1400	 TE Part # 4151009-1 OCEAN-2.0-APPLICATOR-S-090F1400	 TE Part # 4151009-2 OCEAN-2.0-APPLICATOR-S-090F1400	 TE Part # 7-4151009-1 OCEAN-2.0-APPLICATOR-S-090F1400



TE Part # 7-4151009-2
[OCEAN-2.0-APPLICATOR-S-090F1400](#)

KIT
TE Part # 7-4151009-7
[OCEAN_2.0_SPARE_PART_KIT-090F1400](#)

Customers Also Bought

TE Part #1-2199298-3
[14P,DIP SKT,300 CL,LDR,PB FREE](#)

TE Part #4-640441-0
[MTA Receptacle: Nylon, Tin Plated, 2.54 mm](#)

TE Part #640550-6
[06P MTA100 COVER](#)

TE Part #640456-8
[08P MTA100 HDR ASSY F/L SQ STR](#)

TE Part #2-1676913-6
[YR1 0.1% 1K0](#)

TE Part #641994-1
[MTA100 KEYING PLUG W/CARRIER](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5-530501-5_U.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-530501-5_U.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-530501-5_U.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English



DUO-TYNE Flag Contact

English

Application Specification

Japanese

DUP-TYNE Flat Contacts

Japanese

Application Specification

Japanese